

Twist-Lock® Devices

50 Ampere, 125/250, 3Ø 250 Volts and 3Ø 480 Volts AC

3 Pole, 4 Wire Grounding

Plugs, Flanged Inlets, Connector Bodies and Receptacles
IP20
 SUITABILITY


50A
125/250V
 UL/CSA

50A 3Ø
250V AC
 UL/CSA


50A 3Ø
480V AC
 UL/CSA
Plugs

Description	Cord Dia.	Catalog Numbers		
Nylon cover, thermoplastic polyester interior.	.920" - 1.2" (23.68-30.48)	CS6365C	CS8365C	CS8165C

Accessories on page B-60.

**CS6365C****Flanged Inlets**

Description	Catalog Numbers		
Zinc plated steel casing, thermoplastic polyester interior.	CS6375	CS8375	CS8175

**CS6375**
IP20
 SUITABILITY

50A
125/250V
 UL/CSA

50A 3Ø
250V AC
 UL/CSA

50A 3Ø
480V AC
 UL/CSA
Connector Bodies


Description	Cord Dia.	Catalog Numbers		
Nylon cover, thermoplastic polyester interior.	.920" - 1.2" (23.68-30.48)	CS6364C	CS8364C	CS8164C

Accessories on page B-60.

**CS6364C****Receptacles**

Description	Catalog Numbers		
Black melamine.	CS6369	CS8369	CS8169

Accessories on page B-60.

**CS6369**