

(2.00 mm) .0787"

YTW-12-10-S-6-300-215

YTW-26-02-T-5-250-050

YTW-20-03-G-Q-400-085

YTW SERIES

HIGH-DENSITY BOARD STACKER

SPECIFICATIONS

For complete specifications see www.samtec.com/YTW

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Operating Temp Range:
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

RoHS Compliant:

Yes

Lead-Free Solderable:
Wave only


RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




Mates with:
YTQ, YTS, YTE

OTHER SOLUTIONS




Paste In Hole (PIH) processing.
Contact Samtec ASP Group.



(2.00 mm)
.0787" pitch

Choice of 4, 5 or 6 row



Note:
This Series is non-standard,
non-returnable.