



This document is the property of Amphenol Corporation and is delivered on the understanding that it contains neither recommendations nor instructions for use. It is to be used for reference only and is not to be used for manufacturing or assembly. It is not to be used for any other purpose without the written consent of Amphenol Corporation. It is not to be used for any other purpose without the written consent of Amphenol Corporation. It is not to be used for any other purpose without the written consent of Amphenol Corporation.




D-SUB TECHNICAL DATA

SHELL :Steel 2.5um (100u") min tin over 1.25um (50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
CONTACTS : brass.
0.1um(4u") min gold over 1.25um (50u") min nickel
ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
withstanding voltage : 1000V RMS at 50Hz
Current rating: 7.5A.
Insulation resistance >5000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 85°C ,peak at 125°C
MARKING : Amphenol---(Series No.)
Commercial reference
Manufacturing date

REVISIONS			
SYM	ECN	DESCRIPTION	DATE
A			07/02/07

PRODUCT CODE

L77DE09S



UNLESS OTHERWISE SPECIFIED			
TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Iss. revng
+	+	CHECKED	07/02/07
XX	0.50		07/02/07
XX	0.30		
FRACTIONS	0.20		
ANGLES	2°		
FOR MATERIALS AND FINISHES			
SEE NOTES			
REMOVE SHARP EDGES		DRAWING FILE :	
DIMENSIONS		ANGLE OF PROJECTION	
U.S.	INCHES		
METRIC	MM		
TITLE		SIZE	
Amphenol		A4	
Stamped and Formed connector, SD series		C L77DE09S	
		SCALE NONE	
		SHEET 1 OF 1	