







PERFORMANCE CHARACTERISTICS

CURRENT RATING : 1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
RATED VOLTAGE : 500 V AC (CONT / CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE : 20 mΩ MAX
INSERTION FORCE : 0.75 N MAX / CONT
EXTRACTION FORCE : 0.15 N MIN / CONT
INSULATION RESISTANCE : 10⁴ MΩ MIN

- NOTES
- *--* PERFORMANCE LEVEL INDICATION: Z1= PL3 (SEE CAT. NR.) N9= PL2 E9= PL1
 - CSA CERTIFIED, FILE NUMBER LR 44961-51.
UL APPROVED, FILE NUMBER E31151.



FEMALE SIGNAL RIGHT ANGLE PRESS-FIT-TO-BOARD CONNECTOR

WITH SERVICECENTER

1DEC ±0.2 1DEC 2DEC ±0.1 2DEC ANGLES ±1° HOEKEN	APPR. DRAFT CHECKED PROD. MGR. PR.ENG. MGR. PR.MGT. MGR.	DATE 30-03-99 	SIGN. M.Fret 	MILLIPACS 2 / TYPE A / UPPER SHIELDING (ODD POS.) CAT. No. HM2R10PA5108-- FRAMATOME CONNECTORS BELGIUM N.V. A. SPINOYSTRAAT 8, 2800 MECHELEN	SCALE 3 / 1
ALL DIMENSIONS IN MM ALLE AFMETINGEN IN MM				BS,C ,201444,036,02 DRAWING No. CUSTOMER DRAWING	

25-Nov-1999 8:03:47 1

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN HAN HOCH NABEMAKT. HERDRUKT, OVERNAMEAHT AAN DERDEN, HOCH VOOR FABRICATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING, BIJ NIET GEBRUIK IS TERUGZENDING VERPLICHT.