




D

C

B

A



- CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- MOLDED PARTS: NYLON OR POLYESTER, UL 94V-O RATED, BLACK. CLINCH NUTS & SHELLS: CARBON STEEL PER ASTM A109.
- $5.08 \mu\text{m}$ [.000200] MIN TIN OVER $2.54 \mu\text{m}$ [.000100] MIN COPPER.
- .068 MAX DIA WIRE INSULATION SIZE IS RECOMMENDED FOR USE WITH THIS RECEPTACLE.
- CLEAR CHROMATE OVER ZINC.

3		5		4-40		5207661-3	
SHELL FINISH		CLINCH NUT FINISH		CLINCH NUT THREAD TYPE		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 11-10-04 G. ATTADIA - DOCK5		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
				CHK 11-10-04 J. GERACE			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11-10-04 M. WALMSLEY		NAME RECEPTACLE CONNECTOR, SIZE 4, 37 POSN, WITH CLINCH NUTS, AMPLIMITE HDP	
		0 PLC ± -		PRODUCT SPEC 108-40005			
		1 PLC ± -		APPLICATION SPEC			
		2 PLC ± 0.13 [.005]		114-40030		SIZE A2	
		3 PLC ± -					
MATERIAL 2		4 PLC ± -				DRAWING NO C=5207661	
		ANGLES ± 2°					
FINISH SEE TABLE		WEIGHT -					
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	
						REV 0	