

You are here: [Products](#) » [Connectors f.con](#) » [PCB connectors](#) » [Jumpers](#) » [CAB 6 ...](#) » [CAB_06_05_G](#)



- Heatsinks f.cool
- Cases f.case
- ▼ **Connectors f.con**
 - Sockets
 - ▼ PCB connectors
 - Male headers
 - Female headers
 - Direct female connectors
 - **Jumpers**
 - IDC-connectors
 - D-Sub connectors
 - Brackets for PC
 - Optoelectronics


Jumpers

CAB 6 ...

CAB 6 05 G ...

for 0.6...0.64 mm wire wrap pins and Ø 0.6...0.7 mm The flexible contacts are shorting two pins. The jumpers can be mounted behind and next to each other.

add to request



Features Technical Drawing Variants Service

no. of contacts	2
surface contact / contact sleeve	0.5 µm Au 1 µm Au 5 µm Sn
surface of contact	0.5 µm gold
insert depth	5mm...plug through
nominal current	1.5 A
nominal voltage	250 V AC
insulating body material	PA 66
temperature range	-40°C... +105°C
grid	2.54 mm
version	open, for miniature alligator clip
colour	black red blue grey