

Search within category

GO

HB0D2A0BA08W1



The 16A, single-phase 230V horizontal power strip in black has four IEC C-13 and four IEC C-19 receptacles. It features a 10' (3m) power cord with an IEC 60309 - 2P+ E pin in-sleeve connector. It complies with IEC 60950-1, EN 55022, and EN 55024 and is CE Marked. It measures 1.7H x 17.0W x 1.9D (43mm x 432mm x 47mm). It is sold individually.

| Specs                          | Packaging Details                    | Documents | ★ Add to Favorites | 🛒 Add to BOM |
|--------------------------------|--------------------------------------|-----------|--------------------|--------------|
| CE Compliant                   | Yes                                  |           |                    |              |
| Rack PDU Type                  | Basic Rack PDU                       |           |                    |              |
| Monitoring                     | NA                                   |           |                    |              |
| Remote Outlet Switching        | No                                   |           |                    |              |
| Mount Orientation              | Horizontal                           |           |                    |              |
| Current Rating (Amps)          | 16A                                  |           |                    |              |
| Input Voltage                  | 230V - Single Phase                  |           |                    |              |
| Plug Type                      | IEC 60309 - 6H 2P+E Blue Splashproof |           |                    |              |
| Output Voltage                 | 230V                                 |           |                    |              |
| Receptacle Type                | IEC C-13 and IEC C-19                |           |                    |              |
| Total Number of Outlets        | 8                                    |           |                    |              |
| Depth (In.)                    | 1.85                                 |           |                    |              |
| Depth (mm)                     | 47.0                                 |           |                    |              |
| Height (In.)                   | 1.72                                 |           |                    |              |
| Height (mm)                    | 43.7                                 |           |                    |              |
| Width (In.)                    | 17.00                                |           |                    |              |
| Width (mm)                     | 431.8                                |           |                    |              |
| Tool-Less Button Spacing (In.) | NA                                   |           |                    |              |
| Tool-Less Button Spacing (mm)  | NA                                   |           |                    |              |
| No. of Rack Spaces             | 1                                    |           |                    |              |
| Surge Suppression              | No                                   |           |                    |              |
| Amps                           | 16A                                  |           |                    |              |
| Cable Length                   | 3                                    |           |                    |              |
| Length (In.)                   | 22.00                                |           |                    |              |
| UL Recognized                  | No                                   |           |                    |              |
| Voltage                        | 230V                                 |           |                    |              |
| RoHS Compliancy Status         | Compliant                            |           |                    |              |
| Min. Order Qty.                | 1                                    |           |                    |              |