


Dimensions: mm (In.)



Electrical Specifications:

- Rating: 1A/125VAC
- Contact resistance: less than 20mΩ at DC1A
- Insulation resistance: minimum 200MΩ at 500VDC
- Dielectric Strength: 1 minute at 500VDC

Mechanical Specifications:

- Life: more than 30,000 cycles (60/minute)

Materials:

- Knob: ABS plastics (polycarbonate)
- Metal: nickel plated brass
- Nut: nickel plated brass
- Washer: copper wire, uni-chromate plated
- Body: molded black plastics
- Terminals: silver plated brass
- Cap: polycarbonate

| Mouser Stock No. | Type | Circuit | Button Color |
|------------------|--------|------------|--------------|
| 10PA022 | 2PSPST | Off - (On) | Red |
| 10PA023 | 2PSPST | Off - (On) | Black |

Pushbutton Switches

10PA022, 10PA023

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10PA023](#) [10PA022](#)