




REV.	DATE	DESCRIPTION
NC	11/25/02	INITIAL RELEASE



P.C.B. LAYOUT

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	11/25/02								
7						CHECKED										
6						ISSUED										
5						SHEET	1 OF 1			PART DESCRIPTION SMA SURFACE MOUNT JACK —						
4																
3	CONTACT PIN	BER. COPPER	GOLD	1					PART NO. 132134–10							
2	INSULATOR	TEFLON	NATURAL	1												
1	BODY	BRASS	GOLD	1					DWG. NO. 132134–10.DWG							
DESCRIPTION					MATERIAL		FINISH		QTY		REV.	NC	SIZE	A	SCALE	NA