


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638111000](#)
Status: **Active**
Description: Hand Crimper - DISTRIBUTION ONLY

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	T0815
Comments	DISTRIBUTION ONLY
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	TM-638000029
Application Tooling Documents	TM-638000029SP
Sales Drawing	638111000



EU RoHS **China RoHS**
RoHS Compliance
Not Required
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[T0815 Series](#)

Application Tooling Description	FAQ Product #
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	0002062101
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Reel	0002091102
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp	0002061101

Terminal, Female, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	<u>0002061131</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel	<u>0002062103</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag	<u>0002062131</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel	<u>0002062132</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag	<u>0002065100</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm (15µ") Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	<u>0002065101</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm (30µ") Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	<u>0002065102</u>

Brass Contact, 18-24 AWG, Bag	
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38μm (15μ") Gold (Au) Plated Brass Contact, 18-24 AWG, Bag	<u>0002065103</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	<u>0002065108</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38μm (15μ") Gold (Au) Plated Brass Contact, 24-30 AWG, Reel	<u>0002065130</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38μm (15μ") Gold (Au) Plated Brass Contact, 24-30 AWG, Bag	<u>0002065135</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.76μm (30μ") Gold (Au) Plated Brass Contact, 24-30 AWG, Bag	<u>0002066100</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	<u>0002066102</u>

with .76µm (30µ") Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag Packaged 1.57mm (.062")	<u>0002066103</u>
Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm (.062")	<u>0002066119</u>
Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Bag 1.57mm (.062")	<u>0002066130</u>
Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Reel 1.57mm (.062")	<u>0002066135</u>
Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Bag 2.36mm (.093")	<u>0002091104</u>
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Bag 2.36mm (.093")	<u>0002091142</u>
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1433, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel 2.36mm (.093")	<u>0002091144</u>
Diameter, Standard .093" Pin and Socket Crimp	

Terminal, Series 1433, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag	
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Reel	<u>0002092101</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Bag	<u>0002092103</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1434, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel	<u>0002092141</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1434, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag	<u>0002092143</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Gold (Au) Plated Brass Contact, 14-20 AWG, Reel	<u>0002095100</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Selective Gold (Au) Plated Brass Contact, 14-20 AWG, Reel	<u>0002095102</u>
2.36mm (.093") Diameter, Standard .093" Pin and Socket Crimp Terminal, Series	<u>0002095106</u>

1189, Female, with Gold (Au) Plated Brass Contact, 14-20 AWG, Bag	2.36mm (.093")	0002095111
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Selective Gold (Au) Plated Brass Contact, 14-20 AWG, Bag	2.36mm (.093")	0002096100
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Gold (Au) Plated Brass Contact, 14-20 AWG, Reel	2.36mm (.093")	0002096106
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Gold (Au) Plated Brass Contact, 14-20 AWG, Bag	2.36mm (.093")	0002096110
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Selective Gold (Au) Plated Brass Contact, 14-20 AWG, Bag	2.36mm (.093")	0002096145
Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1434, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Bag	1.57mm (.062")	0002065109
Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag	1.57mm (.062")	0002065138

1855, Female, with 0.76µm (30µ") Gold (Au) Plated Brass Contact, 24-30 AWG, Reel	
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Selective Gold (Au) Plated Brass Contact, 24-30 AWG, Reel	<u>0002065147</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Selective Gold (Au) Plated Brass Contact, 24-30 AWG, Bag	<u>0002065148</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm (30µ") Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel Packaged	<u>0002066101</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Reel	<u>0002066118</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Selective Gold (Au) Plated Brass Contact, 24-30 AWG, Reel	<u>0002066138</u>
1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Selective Gold (Au) Plated Brass	<u>0002066139</u>

	Contact, 24-30 AWG, Bag 1.57mm (.062") <u>0002066143</u> Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Selective Gold (Au) Plated Brass Contact, Tin (Sn) Plated Crimp Area, 24-30 AWG, Reel 1.57mm (.062") <u>0002066144</u> Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Selective Gold (Au) Plated Brass Contact, Tin (Sn) Plated Crimp Area, 24-30 AWG, Bag 2.36mm (.093") <u>0002095146</u> Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1433, Female, with Gold (Au) Plated Brass Contact, 24-30 AWG, Reel 2.36mm (.093") <u>0002095147</u> Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1433, Female, with Gold (Au) Plated Brass Contact, 24-30 AWG, Bag 2.36mm (.093") <u>0002096101</u> Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Selective Gold (Au) Plated Brass Contact, 14-20 AWG, Reel 2.36mm (.093") <u>0002096144</u> Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1434, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Reel
--	---

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION