

AG Fuses

Originally stood for "all glass." The automotive industry uses the "AG" prefix (AGC, AGW) for most glass fuses. They vary in length, diameter and amperage rating.

Voltage Rating: 32V AC/DC

SFE Fuses

Glass fuses designed to specifications set by the Society of Fuse Engineers. All are 1/4 inch in diameter, but vary in length according to the ampere rating to ensure accurate fuse replacement. Both AG and SFE fuses were designed into North American vehicles prior to 1981. Glass fuses are also used for auto accessory applications.


Voltage Rating: 32V AC/DC

GBC Fuses

A ceramic type, torpedo shaped fuse that can be currently found in many European cars. Consisting of a heat resistant body, the fuse element stretches over the exterior of the body from end to end. The body varies in color to assist in proper replacement.

Voltage Rating: 32V AC/DC

Glass/Ceramic Fuses



US & Canadian Boxed No.	US Carded No.	Canadian Carded No.
AGA (1AG)		
AGA 1	AGA 1 BP	AGA 1 CABP
AGA 1.5	AGA 1.5 BP	AGA 1.5 CABP
AGA 2	AGA 2 BP	AGA 2 CABP
AGA 2.5	AGA 2.5 BP	AGA 2.5 CABP
AGA 3	AGA 3 BP	AGA 3 CABP
AGA 5	AGA 5 BP	AGA 5 CABP
AGA 6	AGA 6 BP	AGA 6 CABP
AGA 7.5	AGA 7.5 BP	AGA 7.5 CABP
AGA 10	AGA 10 BP	AGA 10 CABP
AGA 15	AGA 15 BP	AGA 15 CABP
AGA 20	AGA 20 BP	AGA 20 CABP
AGA 25	AGA 25 BP	AGA 25 CABP
AGA 30	AGA 30 BP	AGA 30 CABP
AGC (3AG)		
AGC .5	AGC .5 BP	AGC .5 CABP
AGC 1	AGC 1 BP	AGC 1 CABP
AGC 1.5	AGC 1.5 BP	AGC 1.5 CABP
AGC 2	AGC 2 BP	AGC 2 CABP
AGC 2.5	AGC 2.5 BP	AGC 2.5 CABP
AGC 3	AGC 3 BP	AGC 3 CABP
AGC 4	AGC 4 BP	AGC 4 CABP
AGC 5	AGC 5 BP	AGC 5 CABP
AGC 6	AGC 6 BP	AGC 6 CABP
AGC 7.5	AGC 7.5 BP	AGC 7.5 CABP
AGC 8	AGC 8 BP	AGC 8 CABP
AGC 10	AGC 10 BP	AGC 10 CABP
AGC 15	AGC 15 BP	AGC 15 CABP
AGC 20	AGC 20 BP	AGC 20 CABP
AGC 25	AGC 25 BP	AGC 25 CABP
AGC 30	AGC 30 BP	AGC 30 CABP
AGC 35	AGC 35 BP	AGC 35 CABP
AGU (5AG)		
AGU 1	N/A	N/A
AGU 2	N/A	N/A
AGU 3	N/A	N/A
AGU 4	N/A	N/A
AGU 5	N/A	N/A
AGU 10	N/A	N/A
AGU 15	N/A	N/A
AGU 20	N/A	N/A
AGU 25	N/A	N/A
AGU 30	N/A	N/A
AGU 35	N/A	N/A
AGU 40	N/A	N/A
AGU 50	N/A	N/A
AGU 60	N/A	N/A
AGW (7AG)		
AGW 1	AGW 1 BP	AGW 1 CABP
AGW 1.5	AGW 1.5 BP	AGW 1.5 CABP
AGW 2.5	AGW 2.5 BP	AGW 2.5 CABP
AGW 3	AGW 3 BP	AGW 3 CABP
AGW 4	AGW 4 BP	AGW 4 CABP
AGW 5	AGW 5 BP	AGW 5 CABP
AGW 6	AGW 6 BP	AGW 6 CABP
AGW 15	AGW 15 BP	AGW 15 CABP
AGW 20	AGW 20 BP	AGW 20 CABP
AGW 30	AGW 30 BP	AGW 30 CABP
AGX (8AG)		
AGX 2	AGX 2 BP	AGX 2 CABP
AGX 3	AGX 3 BP	AGX 3 CABP
AGX 20	AGX 20 BP	AGX 20 CABP
AGX 25	AGX 25 BP	AGX 25 CABP
AGX 30	AGX 30 BP	AGX 30 CABP
AGY (9AG)		
AGY 50	N/A	N/A
GBC (Ceramic)		
GBC 5 (Yellow)	GBC 5 BP	GBC 5 CABP
GBC 8 (White)	GBC 8 BP	GBC 8 CABP
GBC 16 (Red)	GBC 16 BP	GBC 16 CABP
GBC 25 (Blue)	GBC 25 BP	GBC 25 CABP
SFE		
SFE 4	SFE 4 BP	SFE 4 CABP
SFE 6	SFE 6 BP	SFE 6 CABP
SFE 7.5	SFE 7.5 BP	SFE 7.5 CABP
SFE 9	SFE 9 BP	SFE 9 CABP
SFE 14	SFE 14 BP	SFE 14 CABP
SFE 20	SFE 20 BP	SFE 20 CABP
SFE 30	SFE 30 BP	SFE 30 CABP
UK		
UK 35	UK 35 BP	UK 35 CABP
UK 50	UK 50 BP	UK 50 CABP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[0AGA02.5V](#) [0AGU015.T](#) [0AGU002.T](#) [0SFE030.V](#) [0AGA025.V](#) [0AGU010.T](#) [0AGU004.T](#) [0AGC020.V](#) [0AGW001.V](#)
[0AGC001.V](#) [0AGU003.T](#) [0AGU005.T](#) [0AGA030.V](#) [0AGA020.V](#) [0AGU001.T](#) [0AGC010.V](#) [0AGC003.V](#) [0AGC015.V](#)
[0AGU025.T](#) [0AGC005.V](#) [0AGU035.T](#) [0AGW006.V](#) [0AGC025.V](#) [0AGX003.V](#) [0SFE07.5V](#) [0AGA002.V](#) [0AGX030.V](#)
[0AGA006.V](#) [0AGA010.V](#) [0SFE009.V](#) [0AGC0001ZPGLO](#) [0AGW005.V](#) [0AGX002.V](#) [0AGC02.5V](#) [0AGC030.V](#)
[0AGW003.V](#) [0AGW015.V](#) [0AGW004.V](#) [0AGC035.V](#) [0AGW01.5V](#) [0AGA07.5V](#) [0AGX020.V](#) [0AGA01.5V](#) [0SFE006.V](#)
[0AGW020.V](#) [0AGX025.V](#) [0AGA005.V](#) [0SFE014.V](#) [0AGU050.T](#) [0AGW02.5V](#) [0AGC.500V](#) [0AGA015.V](#)
[0AGW030.V](#) [0AGU040.T](#) [0SFE020.V](#) [0AGA003.V](#) [0SFE004.V](#) [0AGU060.T](#) [0AGC004.V](#) [0AGU030.T](#) [0AGC01.5V](#)
[0AGC07.5V](#) [0AGC008.V](#) [0AGC002.V](#) [0AGU020.T](#) [0AGC006.V](#) [0AGW015.VP](#) [0AGX025.VP](#) [0AGW020.VP](#)
[0AGW0001ZP](#) [0AGW030.VP](#) [0AGX030.VP](#) [0AGW005.VP](#) [0AGX020.VP](#)