





LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					W1	REVISED PER ECO-09-021826	12JAN10	KK	AEG

D

C


B

A



PCB FOOT PRINT DETAIL

- 1 PRELIMINARY – NOT RELEASED FOR PRODUCTION.
- 2 MATTE TIN PLATED
- 3 TIN-LEAD PLATED
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



4 OBSOLETE	23	55.88 [2.200]	60.96 [2.400]	66.04 [2.600]	61.47 [2.420]	3.81 [.150]	3.81 [.150]	7.62 [.300]	3 6-530218-3
	22	53.34 [2.100]	58.42 [2.300]	63.5 [2.500]	58.93 [2.320]	3.81 [.150]	3.81 [.150]	7.62 [.300]	3 5-530218-9
	30	73.66 [2.900]	78.74 [3.100]	83.82 [3.300]	79.25 [3.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	3 5-530218-6
	17	40.64 [1.600]	45.72 [1.800]	50.8 [2.000]	46.23 [1.820]	3.81 [.150]	3.81 [.150]	7.62 [.300]	3 5-530218-5
4 OBSOLETE	25	60.96 [2.400]	66.04 [2.600]	71.12 [2.800]	66.55 [2.620]	3.81 [.150]	3.81 [.150]	7.62 [.300]	3 5-530218-1
	23	55.88 [2.200]	60.96 [2.400]	66.04 [2.600]	61.47 [2.420]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 1-530218-3
	15	35.56 [1.400]	40.64 [1.600]	45.72 [1.800]	41.15 [1.620]	0.381 [.015]	3.81 [.150]	7.62 [.300]	2 1-530218-2
	36	88.9 [3.500]	93.98 [3.700]	99.06 [3.900]	94.49 [3.720]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 1-530218-1
4 OBSOLETE	10	22.86 [.900]	27.94 [1.100]	33.02 [1.300]	28.45 [1.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 1-530218-0
	22	53.34 [2.100]	58.42 [2.300]	63.5 [2.500]	58.93 [2.320]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 -530218-9
	50	124.46 [4.900]	129.54 [5.100]	132.33 [5.210]	130.05 [5.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-8
	40	99.06 [3.900]	104.14 [4.100]	109.22 [4.300]	104.65 [4.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-7
4 OBSOLETE	30	73.66 [2.900]	78.74 [3.100]	83.82 [3.300]	79.25 [3.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-6
	17	40.64 [1.600]	45.72 [1.800]	50.8 [2.000]	46.23 [1.820]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 -530218-5
	20	48.26 [1.900]	53.34 [2.100]	58.42 [2.300]	53.85 [2.120]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-4
	13	30.48 [1.200]	35.56 [1.400]	40.64 [1.600]	36.07 [1.420]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-3
OBSOLETE	18	43.18 [1.700]	48.26 [1.900]	53.34 [2.100]	48.77 [1.920]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-2
	25	60.96 [2.400]	66.04 [2.600]	71.12 [2.800]	66.55 [2.620]	3.81 [.150]	3.81 [.150]	7.62 [.300]	2 530218-1
NO OF POSITIONS		A	B	C	D	L	M	N	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A STAUB_BG CHK H ROSE APVD H ROSE	11AUG93 08FEB94 08FEB94	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		CONNECTOR ASSEMBLY, TWIN LEAF WITH .025 SQ POST, RIGHT ANGLE .100 CENTERS	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APPLICATION SPEC	SIZE A1	CAGE CODE 00779	DRAWING NO 530218
MATERIAL SEE CALLOUT	FINISH SEE CALLOUT	WEIGHT -	CUSTOMER DRAWING		SCALE 4:1
			SHEET 1		OF 1
			REV W1		