





**MALE CONNECTOR WITH FIXING  
FLANGE PIN SPACING 5 MM / 0.197 IN  
100% PROTECTED AGAINST  
MISMATING WITH PRECEDING  
EARTH**  
721-603/019-042 TO 721-605/019-042

|                                                      |                                                                                               |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 721-603/019-042                                                                               |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 2.5                                                                                    |
| Cross section2 (Cross section / AWG)                 | 28 - 12                                                                                       |
| Strip length (Strip length / mm)                     | 8 - 9                                                                                         |
| Measured voltage (Measured voltage / V)              | 320                                                                                           |
| Measured shock voltage (Measured shock voltage / kV) | 4                                                                                             |
| Pollution degree (Pollution degree)                  | 2                                                                                             |
| Current intensity (Current intensity / A)            | 12                                                                                            |
| RM (PIN SPACING / mm)                                | 5                                                                                             |
| P (NO. OF POLES)                                     | 3                                                                                             |
| Height (Height / mm)                                 | 14.3                                                                                          |
| Width (Width / mm)                                   | 29.8                                                                                          |
| Depth (Depth / mm)                                   | 27.5                                                                                          |
| No. of connection Points (No. of connection Points)  | 3                                                                                             |
| No. of potentials (No. of potentials)                | 3                                                                                             |
| COLOR (COLOR)                                        | lichtgrau                                                                                     |
| WEIGHT (WEIGHT / g)                                  | 5.9                                                                                           |
| Comment (Comment)                                    | A = (No. of poles x Pin Spacing) + 3,2 mm   D = A - 0,2 mm   E = D + 5,8 mm   F = D + 11,8 mm |