

SEARCH

[Advanced](#) [Parametric](#)

Products > Display Modules >

10.4-Inch Flat Panel Display

NL6448BC33-64R

Documentation:

For detailed product specifications and datasheet, please contact your local NEC Electronics America [Sales Representative](#).

Display Modules Overview

Product Lineup

Markets

Display Module News

LCD Newsletter

See our newsletter page for the latest issue.

Resolution	640 x 480
Viewing Angle (°L/R)	80/80
Viewing Angle (°U/D)	80/60
Luminance (cd/m ²)	450
Input Signal	Digital 6-bit RGB
Colors	262,144
Dimension HxWxD (mm)	243 x 185.1 x 10.5
Weight (g)	475
Contrast	600:1
Color Gamut (%)	40
Response Ton (ms)	25 (tot)
Supply Voltage LCD (V)	3.3 (5)
Backlights (CCFL)	2
Inverter	No
Power LCD (W)	0.99
Power Backlight (W)	5.2
Total Power (W)	6.2
Absolute Storage Temp (°C)	-20 to 80
Absolute Operating Temp (°C)	-10 to 70
Polarizer Surface	Clear

Additional remarks about this product:

CMOS version of -63D, Clear, Reverse Scan, Replaceable Backlight, UL

Click [here](#) to rate this page