

Control Stations ø 30

► CONTROL STATIONS - NON-ILLUMINATED



Technical Info (p. 147)

SPRING RETURN - FLUSH

Part Number



TBPA301-101

● Green

NO



Legend Text

START

TBPA301-101

● Red

NC



STOP

TBPA301-104

MUSHROOM HEAD ø 40 - SPRING RETURN



TBPA301-201

● Green

NO



Legend Text

START

TBPA301-204

● Red

NC



STOP

TBPA301-201

SELECTOR SWITCH - WITH HANDLE



TBPA301-401

2 Maintained positions - 90°

● Black

NO



Marking

OFF ON

TBPA301-401

SELECTOR SWITCH - WITH KEY



TBPA301-402

Supplied with 2 keys profile n° 455

2 Maintained positions - 90°
Key free in position 0-1

● Black

NO



Marking

OFF ON

TBPA301-402

Control Stations ø 30

► CONTROL STATIONS - NON-ILLUMINATED



Technical Info (p. 147)

MUSHROOM HEAD Ø 40 - MAINTAINED

Part Number



TBPA301-301

Push-turn to reset

● Red NC



EMERGENCY STOP

TBPA301-301

Push-Pull to reset

● Red NC



EMERGENCY STOP

TBPA301-311

Push-Key to reset

● Red NC



EMERGENCY STOP

TBPA301-321

Supplied with 2 keys profile n° 455

SPRING RETURN - FLUSH



TBPA302-001

● Green
● Red

NO
NC



Marking

START
STOP

TBPA302-001

● Black
● Black

NO
NO



UP
DOWN

TBPA302-002

SPRING RETURN - FLUSH



TBPA303-001

● Green
● Red
● Green

NO
NC
NO



Marking

UP
STOP
DOWN


TBPA303-001

Control Stations ø 30

► PRE-DRILLED POLYCARBONATE ENCLOSURES



BPA202



Number of Holes	Cable Gland	Dimensions					Part Number
		L	W	D	A	B	
1	1 x PG13-GY	82	80	55	70	50	BPA301
2	1 x PG13-GY	120	80	55	108	50	BPA302
3	1 x PG13-GY	160	80	55	148	50	BPA303
1	1 x PG13-GY	82	80	85	70	50	BPP301
2	1 x PG13-GY	120	80	85	108	50	BPP302
3	1 x PG13-GY	160	80	85	148	50	BPP303
4	2 x PG16-GY	122	120	85	110	90	BPP304
6	2 x PG16-GY	200	120	75	188	90	BPA306
8	2 x PG16-GY	200	120	75	188	90	BPA308
10	2 x PG16-GY	240	120	100	288	90	BPP310


► EMPTY POLYCARBONATE ENCLOSURES



BNT208



BNT251



L	W	D	Dimensions (mm)		Part Number
			A	B	
65	50	35	53	38	BNT206
82	80	55	70	50	BNT210
82	80	85	70	50	BNT225
120	80	55	108	50	BNT215
120	80	85	108	50	BNT226
122	120	55	110	90	BNT217
122	120	85	110	90	BNT227
160	80	55	148	50	BNT220
160	80	85	148	50	BNT231
200	120	75	188	90	BNT237
200	150	75	188	119	BNT223
240	120	100	228	90	BNT242
240	160	120	228	130	BNT243
250	160	90	238	130	BNT240

CABLE GLANDS



PG16-GY

	Size	Cable Thickness	
● Grey	PG11	3mm - 7mm	PG11-GY
● Grey	PG13.5	6mm - 12mm	PG13-GY
● Grey	PG16	10mm - 14mm	PG16-GY
● Grey	PG21	13mm - 18mm	PG21-GY
● Grey	PG29	18mm - 25mm	PG29-GY