






Recommended PCB Layout
(Top View)

Materials and Finish

Housing Material-
PBT Thermoplastic
UL 94V-0 Rated
Color: Black

Contact Material-
Phosphor Bronze

Contact Plating Options-
Standard- 0.000015" gold on entire
contact, 0.0001" nickel
underplating
-50 Option: 0.000050" gold on entire
contact to comply with FCC
requirements under No. 47 C.F.R
Part 68, Subpart F,
0.0001" nickel underplating

Electrical Characteristics

Insulation Resistance-
500 Megohms Min.

Dielectric Withstanding Voltage-
1000V rms, 60Hz

Contact Resistance-
20 milliohms Max.

Current Rating-
1.5 Amps

Operating Temperature-
-40°C to +85°C

Durability Rating:
500 mating cycles min.

RoHS COMPLIANT
EU Directive 2002/95/EC



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	9/15/05	New Drawing	R. Aguirre	N.Chang	XXXXXX	9/16/05

GLX-N-64M-BLK

Mod. Jack, Rt Ang PCB Mount, short body

6 position, 4 contacts, RoHS Compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GLX-N-64M-BLK](#)