

Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Draw ings
 - PDF-Copper Butt ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) [Search Tips](#) ☐ Within Results

 Text Search: 'SCS3/0-X'

Your search criteria matched only one product, shown below

SCS3/0-X



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range-taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

▪ Part Number	SCS3/0-X
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Copper Butt Splice, standard barrel, 3/0 AWG wire.
▪ Product Type	Compression Connectors - Splices
▪ CSA Certified	Yes
▪ UL Listed	Yes
▪ Length (In.)	2.12
▪ Length (mm)	53.8
▪ Copper Conductor Size	3/0 AWG
▪ Barrel O.D.	.64
▪ Barrel I.D.	.51
▪ Panduit Color Code	Orange
▪ Panduit Die Index No.	P50
▪ Pricing Description	Copper Compression Butt Splice, Standard Barrel, 3/0 AWG
▪ Wire Strip Length (In.)	1
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ Burndy Die Index No.	14
▪ T&B Die Index No.	50
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.