


1907376

THIS DRAWING IS A CONTROLLED DOCUMENT.

USED ON

Restricted to: General Release



Connector(s): LC-Duplex Secure
 Mode: SM
 Housing Color: Yellow
 Geom. Spec: N/A

Number of Fibers: 2
 Mode: SM
 Jacket Diameter: 2.0 mm
 Jacket Color: Yellow
 FiberType: SM

LC strain relief - 1.6 to 2.0 mm cable
 Color: Blue/Blue

Notes:

- 1 Includes dust caps (not shown on print).
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY BY THE PERSONNEL TO WHOM IT HAS BEEN ISSUED. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
 CE
 DIST
 16

A	Rev Per EC#	RELEASE	5/25/2006	-			
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .	
1 PLC ± .	
2 PLC ± .	
3 PLC ± .	
4 PLC ± .	

Customer Print

DIN	Cable Assy Configurator	MATERIAL		HEAT TREAT	
CHK	Cable Assy Configurator				
APVD	Refer to Engineering Change	Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
NAME	FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail - (1.6 to 2.0mm)				
SCALE	SIZE	DRAWING NO	SHEET	REV	
NTS	A2	C- 1907376	1 of 3	A	

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

D

C

B

A


THIS DRAWING IS A CONTROLLED DOCUMENT.


Part #	L (meters)	LC-Duplex Secure, Yellow		Right Side - No Connector	
		IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907376-1	0.950 - 1.050	0.35	45	-	-
0-1907376-2	1.950 - 2.050	0.35	45	-	-
0-1907376-3	2.950 - 3.050	0.35	45	-	-
0-1907376-4	3.920 - 4.080	0.35	45	-	-
0-1907376-5	4.920 - 5.080	0.35	45	-	-
0-1907376-6	5.920 - 6.080	0.35	45	-	-
0-1907376-7	6.920 - 7.080	0.35	45	-	-
0-1907376-8	7.920 - 8.080	0.35	45	-	-
0-1907376-9	8.850 - 9.150	0.35	45	-	-
1-1907376-0	9.850 - 10.150	0.35	45	-	-
1-1907376-1	10.850 - 11.150	0.35	45	-	-
1-1907376-2	11.850 - 12.150	0.35	45	-	-
1-1907376-3	12.850 - 13.150	0.35	45	-	-
1-1907376-4	13.850 - 14.150	0.35	45	-	-
1-1907376-5	14.850 - 15.150	0.36	45	-	-
1-1907376-6	15.840 - 16.160	0.36	45	-	-
1-1907376-7	16.830 - 17.170	0.36	45	-	-
1-1907376-8	17.820 - 18.180	0.36	45	-	-
1-1907376-9	18.810 - 19.190	0.36	45	-	-
2-1907376-0	19.800 - 20.200	0.36	45	-	-
2-1907376-1	20.790 - 21.210	0.36	45	-	-
2-1907376-2	21.780 - 22.220	0.36	45	-	-
2-1907376-3	22.770 - 23.230	0.36	45	-	-
2-1907376-4	23.760 - 24.240	0.36	45	-	-
2-1907376-5	24.750 - 25.250	0.36	45	-	-
2-1907376-6	25.740 - 26.260	0.36	45	-	-
2-1907376-7	26.730 - 27.270	0.36	45	-	-
2-1907376-8	27.720 - 28.280	0.36	45	-	-
2-1907376-9	28.710 - 29.290	0.37	45	-	-
3-1907376-0	29.700 - 30.300	0.37	45	-	-
3-1907376-1	30.690 - 31.310	0.37	45	-	-
3-1907376-2	31.680 - 32.320	0.37	45	-	-
3-1907376-3	32.670 - 33.330	0.37	45	-	-
3-1907376-4	33.660 - 34.340	0.37	45	-	-
3-1907376-5	34.650 - 35.350	0.37	45	-	-
3-1907376-6	35.640 - 36.360	0.37	45	-	-
3-1907376-7	36.630 - 37.370	0.37	45	-	-
3-1907376-8	37.620 - 38.380	0.37	45	-	-
3-1907376-9	38.610 - 39.390	0.37	45	-	-
4-1907376-0	39.600 - 40.400	0.37	45	-	-
5-1907376-0	49.500 - 50.500	0.38	45	-	-

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES STATED HEREIN. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

A	Rev Per ECH	RELEASE	5/25/2006	-			
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters

 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ± .
 1 PLC ± .
 2 PLC ± .
 3 PLC ± .
 4 PLC ± .

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
OK	Cable Assy Configurator	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Refer to Engineering Change				
NAME	FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail - (1.6 to 2.0mm)				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1907376
SHEET	2 of 3	REV	A		

Customer Print

D
C
B
A

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

A	Rev Per EC#	RELEASE	5/25/2006	-				
P	LTR	REVISION RECORD	DATE	DIN	APVD			

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .	1 PLC ± .
2 PLC ± .	3 PLC ± .
4 PLC ± .	

Customer Print

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Cable Assy Configurator		
APVD	Refer to Engineering Change	Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail - (1.6 to 2.0mm)		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1907376	3 of 3
			REV
			A

D
C
B
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[5-2111981-2](#)