






REV. C

DCO 300855

TOLERANCES ±.010" - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C

~~RESISTANCE~~

CURRENT: 30mA MAX.

NOMINAL VOLTAGE

115 VAC - 50/400Hz

MUST OPERATE

70.0 VAC MAX., 50/400Hz

MUST RELEASE

25.0 VAC MAX., 8.0 VAC MIN., 50/400 Hz

ENVIRONMENT:

VIBRATION 33 Hz TO 3000 Hz @ 30 g's

SHOCK 200 g's 6 MS. DURATION


TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE TIME 15 mS MAX.

RELEASE TIME 50 mS MAX.

CONTACT BOUNCE 1 mS MAX.

CUSTOMER DATA SHEET



CONTACT RATING:

10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE.

100,000 OPERATIONS

DR. B.D. 07MAR2008

CK. J.M.B. 5/14/08

Tyco Electronics

©COPYRIGHT 2005

TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG ITEM

TE NUMBER

CII PART NUMBER

CUST. NO. REV.

1-1617752-6

FC A-210-DY9