



Sample photo

Order symbol: PC 050705
Product nbr: 7032520
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074003607
El. number:
Finland: 3423424
Denmark: 8212002526
Italy: 7301010
Sweden: 2536105
Norway: 2536601

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		65	50	45	Ingress Protection (EN 60529): IP 66/67
inch:		2.6	2.0	1.8	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Fimko
Short term:		-40 ... 250 °F			Europe EN 62208: 2003
Continuous:		-40 ... 175 °F			UL Canada
Accessories:					Gost R
TM 0505		Mounting plate			
TM 0507		Mounting plate			
TRM 0507		DIN-15 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 62262): IK 08/07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:
Underwriters Laboratories
Fimko
Europe EN 62208: 2003
UL Canada
Gost R

EURONORD PC/ABS 65x50x45

