

Cabinets VisionCab



[Click on Image for Larger View](#)

Design Features

- Highly styled and versatile steel cabinet suitable for housing a variety of 19" panel width and EIA-310 compatible equipment.
- Four adjustable L-shaped mounting rails with square holes on EIA spacing; rails will accept either #12-24 (Bud #307) or M6 (#851-DLH) cage nuts.
- Supplied with See-Thru removable front door with tempered glass window.
- Supplied with one fixed ventilated steel shelf.
- Solid steel removable side panels.
- Style A (no suffix) has closed rear (no rear access) with secure wall mounting brackets.
- Style B (-B suffix) has removable rear panel (rear access).
- Equipped with 110V AC, 65 CFM exhaust fan for cooling.
- Cable access holes on top and bottom.
- Supplied with steel wall mounting bracket.
- Four mar resistant feet on bottom surface.
- Finish: Smooth Black Powder Coating

VISION CAB

Catalog Number Style A	Drawings	Catalog Number Style B	Drawings	"U"	Height	Width	Depth	Weight (lbs)
VC-9920	PDF DXF	-	-	6	14.49"	23.62"	17.72"	50
VC-9921	PDF DXF	-	-	9	19.72"	23.62"	17.72"	57
VC-9922	PDF DXF	-	-	12	25.00"	23.62"	17.72"	69
VC-9923	PDF DXF	-	-	15	30.27"	23.62"	17.72"	80
VC-9924	PDF DXF	-	-	18	35.40"	23.62"	17.72"	89
VC-9930	PDF DXF	VC-9930-B	N/A	6	14.49"	23.62"	23.62"	56
VC-9931	PDF DXF	VC-9931-B	N/A	9	19.72"	23.62"	23.62"	66
VC-9932	PDF DXF	VC-9932-B	N/A	12	25.00"	23.62"	23.62"	83
VC-9933	PDF DXF	VC-9933-B	N/A	15	30.27"	23.62"	23.62"	100
VC-9934	PDF DXF	VC-9934-B	N/A	18	35.40"	23.62"	23.62"	117

N/A - Contact Factory