



| Part Number                                                        | Pieces Per Package | Material               | Color  | Labels Per Row | Label Width Inch (mm)<br>A | Label Height Inch (mm)<br>B | Horizontal Repeat Inch (mm)<br>C | Vertical Repeat Inch (mm)<br>D | Web Width Inch (mm)<br>E |
|--------------------------------------------------------------------|--------------------|------------------------|--------|----------------|----------------------------|-----------------------------|----------------------------------|--------------------------------|--------------------------|
| <b>0.400" Label Width — 6 or 8 lines per inch</b>                  |                    |                        |        |                |                            |                             |                                  |                                |                          |
| DAT-179-619-10                                                     | 10,000             | Polyester              | White  | 16             | 0.400 (10.16)              | 0.200 (5.08)                | 0.500 (12.70)                    | 0.250 (6.35)                   | 8.900 (226.06)           |
| DAT-179-652-10                                                     | 10,000             | Polyimide              | Amber  | 16             | 0.400 (10.16)              | 0.200 (5.08)                | 0.500 (12.70)                    | 0.250 (6.35)                   | 8.900 (226.06)           |
| <b>0.500" Label Width — 6 or 8 lines per inch</b>                  |                    |                        |        |                |                            |                             |                                  |                                |                          |
| DAT-67-499-10                                                      | 10,000             | Nylon Cloth            | White  | 12             | 0.500 (12.70)              | 0.750 (19.05)               | 0.600 (15.24)                    | 1.000 (25.40)                  | 8.100 (205.74)           |
| DAT-67-502-10                                                      | 10,000             | Vinyl Cloth            | White  | 12             | 0.500 (12.70)              | 0.750 (19.05)               | 0.600 (15.24)                    | 1.000 (25.40)                  | 8.100 (205.74)           |
| DAT-68-632-10                                                      | 10,000             | Polyvinylfluoride      | White  | 12             | 0.500 (12.70)              | 0.750 (19.05)               | 0.600 (15.24)                    | 1.000 (25.40)                  | 8.100 (205.74)           |
| DAT-31-502*-10                                                     | 10,000             | Vinyl Cloth            | White  | 14             | 0.500 (12.70)              | 0.750 (19.05)               | 0.600 (15.24)                    | 1.000 (25.40)                  | 9.300 (236.22)           |
| DAT-32-632*-10                                                     | 10,000             | Polyvinylfluoride      | White  | 14             | 0.500 (12.70)              | 0.750 (19.05)               | 0.600 (15.24)                    | 1.000 (25.40)                  | 9.300 (236.22)           |
| DAT-21-110-10                                                      | 10,000             | Saturated Paper        | White  | 12             | 0.500 (12.70)              | 1.437 (36.50)               | 0.600 (15.24)                    | 1.500 (38.10)                  | 8.100 (205.74)           |
| DAT-24-502-10                                                      | 10,000             | Vinyl Cloth            | White  | 12             | 0.500 (12.70)              | 1.437 (36.50)               | 0.600 (15.24)                    | 1.500 (38.10)                  | 8.100 (205.74)           |
| <b>0.500" Label Width — 6 or 8 lines per inch — Square Corners</b> |                    |                        |        |                |                            |                             |                                  |                                |                          |
| DAT-43-502-10                                                      | 10,000             | Vinyl Cloth            | White  | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-44-607-10                                                      | 10,000             | Tamper-Resistant Vinyl | White  | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-45-619-10                                                      | 10,000             | Polyester              | White  | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-46-693-10                                                      | 10,000             | Metallized Polyester   | Silver | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-46-969-10                                                      | 10,000             | Metallized Polyester   | Silver | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-98-673-10                                                      | 10,000             | Polyester              | Silver | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| DAT-143-502-10                                                     | 10,000             | Vinyl Cloth            | White  | 16             | 0.500 (12.70)              | 0.937 (23.80)               | 0.500 (12.70)                    | 1.000 (25.40)                  | 9.000 (228.60)           |
| DAT-144-632-10                                                     | 10,000             | Polyvinylfluoride      | White  | 16             | 0.500 (12.70)              | 0.937 (23.80)               | 0.500 (12.70)                    | 1.000 (25.40)                  | 9.000 (228.60)           |
| DAT-171-652-10                                                     | 10,000             | Polyimide              | Amber  | 16             | 0.500 (12.70)              | 0.437 (11.10)               | 0.500 (12.70)                    | 0.500 (12.70)                  | 9.000 (228.60)           |
| <b>0.650" Label Width — 6 or 8 lines per inch</b>                  |                    |                        |        |                |                            |                             |                                  |                                |                          |
| DAT-15-502-1-10                                                    | 10,000             | Vinyl Cloth            | White  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-16-607-10                                                      | 10,000             | Tamper-Resistant Vinyl | White  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-17-619-10                                                      | 10,000             | Polyester              | White  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-56-637-10                                                      | 10,000             | Tedlar®                | White  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-58-652-10                                                      | 10,000             | Polyimide              | Amber  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-88-693-10                                                      | 10,000             | Polyester              | Silver | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-88-969-10                                                      | 10,000             | Polyester              | Silver | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-109-658-10                                                     | 10,000             | Polyimide              | Amber  | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| DAT-111-164-10                                                     | 10,000             | Polyester              | Silver | 10             | 0.650 (16.51)              | 0.200 (5.08)                | 0.800 (20.32)                    | 0.250 (6.35)                   | 8.850 (224.79)           |
| <b>0.750" Label Width — 6 lines per inch</b>                       |                    |                        |        |                |                            |                             |                                  |                                |                          |
| DAT-25-502-10                                                      | 10,000             | Vinyl Cloth            | White  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-26-607-10                                                      | 10,000             | Tamper-Resistant Vinyl | White  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-27-619-10                                                      | 10,000             | Polyester              | White  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-89-969-10                                                      | 10,000             | Polyester              | Silver | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-96-652-10                                                      | 10,000             | Polyimide              | Amber  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-110-658-10                                                     | 10,000             | Polyimide              | Amber  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-112-164-10                                                     | 10,000             | Polyester              | Silver | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |
| DAT-161-637-10                                                     | 10,000             | Polyvinylfluoride      | White  | 9              | 0.750 (19.05)              | 0.250 (6.35)                | 0.900 (22.86)                    | 0.330 (8.46)                   | 9.000 (228.60)           |

Tedlar® is a registered trademark of DuPont.

\* Size does not fit narrow carriage (80-column) printers. See p. 158 for identical narrow carriage labels.

**Note:** Labels in chart are sorted in order by width, height, 3 digit material number (within part number), then die number (within part number).