

17 Series

RoHS
Compliant

NYLON 6.6

GENERAL PURPOSE

MATERIAL OPERATING TEMPERATURE: -40°C to +85°C

APPLICATION OPERATING TEMPERATURE: -10°C to +85°C

APPROVALS¹: cUL_{us}

Part Number	Width mm [Inch]	Length mm [Inch]	Max Bundle Diameter mm [Inch]	Min Loop Tensile Kg [lb]
M - 18lb				
17-M80	2.5 [.098]	80 [3.2]	14.0 [0.55]	8 [18]
17-M100	2.5 [.098]	100 [4.0]	20.5 [0.80]	8 [18]
17-M120	2.5 [.098]	120 [4.7]	27.0 [1.06]	8 [18]
17-M130	2.5 [.098]	130 [5.0]	30.0 [1.18]	8 [18]
17-M150	2.5 [.098]	150 [6.0]	36.5 [1.43]	8 [18]
17-M160	2.5 [.098]	160 [6.3]	39.8 [1.56]	8 [18]
17-M200	2.5 [.098]	200 [8.0]	52.5 [2.06]	8 [18]
17-M260	2.5 [.098]	260 [10.2]	71.6 [2.81]	8 [18]
I - 40lb				
17-I140	3.6 [.14]	140 [5.5]	33.0 [1.30]	18 [40]
17-I150	3.6 [.14]	150 [6.0]	36.0 [1.41]	18 [40]
17-I180	3.6 [.14]	180 [7.0]	46.0 [1.81]	18 [40]
17-I200	3.6 [.14]	200 [8.0]	52.5 [2.06]	18 [40]
17-I250	3.6 [.14]	250 [10.0]	68.0 [2.67]	18 [40]
17-I280	3.6 [.14]	280 [11.0]	78.0 [3.07]	18 [40]
17-I300	3.6 [.14]	300 [11.8]	84.0 [3.30]	18 [40]
17-I370	3.6 [.14]	370 [14.5]	106.0 [4.17]	18 [40]
S - 50lb				
17-S120	4.6 [.181]	120 [4.7]	23.8 [0.93]	22 [50]
17-S160	4.6 [.181]	160 [6.3]	36.6 [1.32]	22 [50]
17-S180	4.8 [.189]	180 [7.0]	43.0 [1.68]	22 [50]
17-S190	4.8 [.189]	190 [7.5]	46.0 [1.81]	22 [50]
17-S200	4.8 [.189]	200 [8.0]	49.5 [1.94]	22 [50]
17-S250	4.8 [.189]	250 [10.0]	65.0 [2.55]	22 [50]
17-S280	4.8 [.189]	280 [11.0]	74.8 [2.94]	22 [50]
17-S300	4.8 [.189]	300 [11.8]	81.0 [3.18]	22 [50]
17-S350	4.8 [.189]	350 [13.7]	97.0 [3.81]	22 [50]
17-S360	4.8 [.189]	360 [14.0]	100.0 [3.93]	22 [50]
17-S370	4.8 [.189]	370 [14.5]	103.5 [4.07]	22 [50]
17-S380	4.8 [.189]	380 [15.0]	106.7 [4.20]	22 [50]
17-S390	4.8 [.189]	390 [15.3]	110.0 [4.33]	22 [50]
17-S400	4.8 [.189]	400 [15.7]	113.1 [4.45]	22 [50]
17-S430	4.8 [.189]	430 [17.0]	122.5 [4.82]	22 [50]
17-S450	4.8 [.189]	450 [17.7]	129.0 [5.07]	22 [50]
17-S500	4.8 [.189]	500 [19.7]	145.0 [5.70]	22 [50]
17-S550	4.8 [.189]	550 [21.6]	160.9 [6.33]	22 [50]
HD - 120lb				
17-HD150	7.6 [.300]	150 [6.0]	35.0 [1.37]	55 [120]
17-HD200	7.6 [.300]	200 [8.0]	50.9 [2.00]	55 [120]
17-HD220	7.6 [.300]	220 [8.6]	57.2 [2.25]	55 [120]
17-HD250	7.6 [.300]	250 [10.0]	66.8 [2.62]	55 [120]
17-HD300	7.6 [.300]	300 [11.8]	82.8 [3.25]	55 [120]
17-HD350	7.6 [.300]	350 [13.7]	98.5 [3.87]	55 [120]
17-HD365	7.6 [.300]	365 [14.0]	103.5 [4.07]	55 [120]
17-HD380	7.6 [.300]	380 [15.0]	108.0 [4.25]	55 [120]
17-HD400	7.6 [.300]	400 [15.7]	114.5 [4.50]	55 [120]
17-HD450	7.6 [.300]	450 [17.0]	130.5 [5.13]	55 [120]
17-HD540	7.6 [.300]	540 [21.0]	159.0 [6.25]	55 [120]
17-HD550	7.6 [.300]	550 [21.6]	162.5 [6.39]	55 [120]
17-HD750	7.6 [.300]	750 [29.5]	226.1 [8.90]	55 [120]

Notes:

1. 17-EHD750, 17-M260HSN, 17-M260HSB, 17-S550HSN, 17-S550HSB, 17-HD750HSN, 17-HD750HSB, 17-M260HT, 17-S550HT, 17-HD750HT, 17-EHD400HT, 17-EHD450HT, 17-EHD500HT, 17-EHD550HT, 17-EHD610HT, 17-EHD760HT, 17-EHD780HT, 17-EHD810HT, 17-EHD920HT, 17-EHD1220HT, 17-EHD750UVB, are not UL approved
Material/Color LT and V0 are not UL approved



17 Series

RoHS
Compliant

NYLON 6.6

GENERAL PURPOSE

MATERIAL OPERATING TEMPERATURE: -40°C to +85°C

APPLICATION OPERATING TEMPERATURE: -10°C to +85°C

APPROVALS¹:  US



Part Number	Width mm [Inch]	Length mm [Inch]	Max Bundle Diameter mm [Inch]	Min Loop Tensile Kg [lb]
EHD - 175lb				
17-EHD400	8.8 [.345]	400 [15.7]	115.0 [4.52]	80 [175]
17-EHD450	8.8 [.345]	450 [18.0]	130.5 [5.13]	80 [175]
17-EHD500	8.8 [.345]	500 [19.7]	146.5 [5.76]	80 [175]
17-EHD550	8.8 [.345]	550 [21.6]	163.5 [6.43]	80 [175]
17-EHD610	8.8 [.345]	610 [24.0]	181.5 [7.14]	80 [175]
17-EHD750	8.8 [.345]	750 [29.5]	226.5 [9.91]	80 [175]
17-EHD760	8.8 [.345]	760 [30.0]	229.5 [9.03]	80 [175]
17-EHD780	8.8 [.345]	780 [30.5]	235.5 [9.27]	80 [175]
17-EHD810	9.0 [.350]	810 [32.0]	245.0 [9.64]	80 [175]
17-EHD920	9.0 [.350]	920 [36.0]	280.0 [11.0]	80 [175]
17-EHD1220	9.0 [.350]	1220 [48.0]	375.5 [14.7]	80 [175]
HSD - 250lb				
17-HSD530	12.4 [.490]	530 [21.0]	156.0 [5.90]	110 [250]
17-HSD650	12.4 [.490]	650 [25.5]	195.0 [7.60]	110 [250]
17-HSD1000	12.4 [.490]	1000 [40.0]	305.0 [12.0]	110 [250]
17-HSD1030	12.4 [.490]	1030 [40.5]	315.0 [12.4]	110 [250]

Notes:

1. 17-EHD750, 17-M260HSN, 17-M260HSB, 17-S550HSN, 17-S550HSB, 17-HD750HSN, 17-HD750HSB, 17-M260HT, 17-S550HT, 17-HD750HT, 17-EHD400HT, 17-EHD450HT, 17-EHD500HT, 17-EHD550HT, 17-EHD610HT, 17-EHD760HT, 17-EHD780HT, 17-EHD810HT, 17-EHD920HT, 17-EHD1220HT, 17-EHD750UVB, are not UL approved
Material/Color LT and V0 are not UL approved

PART NUMBER SYSTEM

17 - **EHD** **610** **B** - **M**

SERIES

CROSS SECTION

LENGTH

MATERIAL/COLOR

N: Natural	Y: Yellow
WH: White	R: Red
B: Normal UV Black	P: Purple
UVB: Weather Resistant Black	BR: Brown
HSB: Heat Stabilized Black	GR: Gray
HSN: Heat Stabilized Natural	O: Orange
HT: High Heat Resistant Natural	FG: Fluorescent Green
LT: Low Temperature Resistant Natural	FL: Fluorescent Yellow
V0: Flame Retardant Natural	FB: Fluorescent Blue
G: Green	FO: Fluorescent Orange
BL: Blue	S: Silver

PACKAGE SIZE

L: 50PCS
C: 100PCS
D: 500PCS
M: 1000PCS
Number: Other Quantity



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[17-EHD1220B-L](#) [17-EHD1220N-L](#) [17-HSD1000N-C](#) [17-HSD1000N-L](#) [17-HSD1030B-C](#) [17-HSD1030N-L](#) [17-EHD780B-C](#) [17-EHD780B-L](#) [17-EHD780N-C](#) [17-EHD780N-L](#) [17-EHD920B-L](#) [17-EHD920N-C](#) [17-HSD530N-C](#) [17-HD540B-L](#) [17-HD550B-C](#) [17-HD550B-L](#) [17-HD550N-C](#) [17-HD550N-L](#) [17-HD750B-C](#) [17-HD750N-L](#) [17-M80B-C](#) [17-M80N-C](#) [17-M80N-M](#) [17-EHD1220B-C](#) [17-EHD1220N-C](#) [17-HSD1000B-C](#) [17-HSD1000B-L](#) [17-HSD1030B-L](#) [17-HSD1030N-C](#) [17-EHD400B-C](#) [17-EHD400B-L](#) [17-EHD400N-C](#) [17-EHD400N-L](#) [17-EHD450B-C](#) [17-EHD450B-L](#) [17-EHD450N-C](#) [17-EHD450N-L](#) [17-EHD500B-C](#) [17-EHD500B-L](#) [17-EHD500N-C](#) [17-EHD500N-L](#) [17-EHD550B-C](#) [17-EHD550B-L](#) [17-EHD550N-C](#) [17-EHD550N-L](#) [17-EHD610B-C](#) [17-EHD610B-L](#) [17-EHD610N-C](#) [17-EHD610N-L](#) [17-EHD750B-C](#) [17-EHD750B-L](#) [17-EHD750N-C](#) [17-EHD750N-L](#) [17-EHD760B-C](#) [17-EHD760B-L](#) [17-EHD760N-C](#) [17-EHD760N-L](#) [17-EHD810B-C](#) [17-EHD810B-L](#) [17-EHD810N-C](#) [17-EHD810N-L](#) [17-EHD920B-C](#) [17-EHD920N-L](#) [17-HSD530B-C](#) [17-HSD530B-L](#) [17-HSD530N-L](#) [17-HSD650B-C](#) [17-HSD650B-L](#) [17-HSD650N-C](#) [17-HSD650N-L](#) [17-HD150B-C](#) [17-HD150N-C](#) [17-HD200B-C](#) [17-HD200N-C](#) [17-HD220B-C](#) [17-HD220N-C](#) [17-HD250B-C](#) [17-HD250N-C](#) [17-HD300B-C](#) [17-HD300N-C](#) [17-HD350B-C](#) [17-HD350N-C](#) [17-HD365B-C](#) [17-HD365N-C](#) [17-HD380B-C](#) [17-HD380N-C](#) [17-HD400B-C](#) [17-HD400N-C](#) [17-HD450B-C](#) [17-HD450N-C](#) [17-HD540B-C](#) [17-HD540N-C](#) [17-HD540N-L](#) [17-HD750B-L](#) [17-HD750N-C](#) [17-I140B-C](#) [17-I140B-M](#) [17-I140N-C](#) [17-I140N-M](#) [17-I150B-C](#)