




QR06 Series

Crossflow Blower



455... 495mm x Ø 88mm 19" Rack Mount Unit

- AC blower with single phase motor. 90° air flow. Ball bearings and terminals. Max ambient temperature of 60 C.
- Wide, even air flow distribution. "V" shaped guide vane suppresses noise.
- Fan propeller of aluminium and air duct housing of sheet steel.
- Rotational direction CW looking at rotor.
- UL, CSA, VDE approvals on some models. Please contact application engineering


19" Rack Mount Unit (Ready for installation)
Shipped complete with:

- Capacitor prewired to terminal block
- Filter mat and retainer included
- Front plate and motor painted black

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Wgt. (lbs)
QR06A-2/106349	1	190	115	50/60	38	55	40	Ball	Leads	3	6.00
QR06A-2/106351	1	190	115	50/60	38	55	40	Ball	Leads	3	6.00
QR06A-2/106350	1	190	230	50/60	41	55	40	Ball	Leads	1	6.00
QR06A-2/106352	1	190	230	50/60	41	55	40	Ball	Leads	1	6.00



PART NUMBER	a	b
QR06A-2/106349	14.96 (380)	18.11 (460)
QR06A-2/106351	14.96 (380)	18.11 (460)
QR06A-2/106350	16.54 (420)	19.69 (500)
QR06A-2/106352	16.54 (420)	19.69 (500)



ebmpapst

e-mail: sales@us.ebmpapst.com - TEL: 860-674-1515 - FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2004 © ebm-papst Inc. reserves the right to change any specifications or data without notice