




REV.	DATE	DESCRIPTION
NC	01/13/03	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S

NOTE:
1. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	01/13/03											
7						CHECKED													
6						ISSUED				PART DESCRIPTION									
5											SMB DIRECT SOLDER PLUG (FOR .141” SEMI RIGID CABLE)								
4										PART NO. 142321									
3	CONTACT PIN	BER. COPPER	GOLD	1						DWG. NO.		142321.DWG		REV.	NC	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1						CAD FILE		C:/142/142321.DWG							
1	BODY	BRASS	GOLD	1						DO NOT SCALE DRAWING									
DESCRIPTION					MATERIAL	FINISH	QTY												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142321](#)