




JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
24E1	24.0	.035	.160	2.01	8,000	C-2F
24B1	24.0	.040	.239	3.00	4,000	C-2F
24C1	24.0	.072	.278	3.49	6,000	C-2V
35A1	35.0	.040	.239	3.00	7,500	C-2F
48D1	48.0	.021	.160	2.01	20,000	CC-2F
55C1	55.0	.050	.478	6.01	5,000	CC-2F

			METRIC THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
							TITLE T-2 TELEPHONE SLIDE BASE ANSI #1			
A ADD PART NO. 24C1 RELEASED			4/11/07 8/16/00		L. WENGSTROM S.C. 4/11/07		SIZE A FSCM NO. 55335		DRAWING NO. SLIDE BASE ANSI #1	
REV. NO. DESCRIPTION/ECO NUMBER			APPVD DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 8/16/00	
							REVISION DATE 4/11/07		REV. NO. A SHEET 1 OF 1	