

KNIPEX-Cobra Water Pump Pliers



6 sizes for
workpieces up
to 120 mm



New product features of Cobra
in 250 mm and 300 mm length:

- ▶ 30% expanded gripping capacity
- ▶ more comfortable hand position
due to optimized fine adjustment
- ▶ improved access to the
workpiece
- ▶ increased load capacity having
a slim design

NEW

KNIPEX Quality – Made in Germany

KNIPEX Cobra Water Pump Pliers

The Cobra grips firmly and securely also under rough conditions.



The special jaw design with opposing off-set teeth ensures maximum grip and perfect alignment. In addition the Cobra offers a unique adjustment mechanism: at the push of a button the tool adjusts fast and easily to the workpiece. No more guessing at the right size.

To the contrary: place the upper part of the jaw against the workpiece, press button and push the lower jaw into position. Simply perfect. The button serves as a memory button: an unintentional adjustment – even under load – is not possible. The fine adjustment always provides a favourable position of the handles. Also in this respect the ergonomically designed Cobra is particularly user friendly.



Gripping-surface
with special
hardened teeth
= wear resistant and
high gripping security

Self-locking on pipes and nuts
= no slipping off the workpiece,
no knuckle-busting

Push-Button-Mechanism
= adjustment at the push
of a button directly on the
workpiece

Fine-adjustment
= optimum adjustment to
different sized workpieces

Box-joint design
= directional stability


Guard
= avoids finger-pinching

Handle cover
= non-slip





Opposing off-set teeth provide a self-gripping effect which avoids slipping off the workpiece



Operation on pneumatic pipes







The Cobra XL (length 400 mm / 16") with a capacity of up to 95 mm / 3 1/2" exceeds by far the efficiency of a pipe wrench of the same length



Mini-Cobra: pocket size with adequate tool function. Capacity up to 30 mm diameter

KNIPEX-Cobra

Article-No.	EAN 4003773-	Finish			Adjustement positions		
87 01 150	060116	head polished, handles plastic coated	1 1/4"	30 mm	11	150	135
87 01 180	022015		1 1/4"	30 mm	11	180	160
87 01 250	022022		2"	46 mm	25	250	300
87 01 300	034087		2 3/4"	60 mm	30	300	515
87 01 400	005636		3 1/2"	95 mm	27	400	1205
87 01 560	044321		4 1/2"	120 mm	20	560	2740
87 02 180	042396	head polished, with two-colour dual component handles	1 1/4"	30 mm	11	180	185
87 02 250	040316		2"	46 mm	25	250	360
87 02 300	029144		2 3/4"	60 mm	30	300	565
87 03 180	005667	head chrome plated, handles plastic coated	1 1/4"	30 mm	11	180	165
87 03 250	043805		2"	46 mm	25	250	320
87 03 300	041382		2 3/4"	60 mm	30	300	515
87 05 250	005681	head chrome plated, with two-colour dual component handles	2"	46 mm	25	250	340
87 05 300	014126		2 3/4"	60 mm	30	300	565
Cobra...matic for one-hand operation			1 1/4"	30 mm	11	180	155
87 11 180	026921	head polished, handles plastic coated	1 1/4"	30 mm	11	180	155
87 11 250	035473		2"	46 mm	25	250	300
Cobra ES – ExtraSlim			1 1/4"	42 mm	19	250	310
87 51 250	061267	head polished, handles plastic coated	1 1/4"	42 mm	19	250	310

MM with opening spring

- Push-Button-Action directly on the workpiece: fast and comfortable operation
- fine adjustment: allows optimum adjustment to different sized workpieces and a comfortable position of the handles
- secure catching of the hinge bolt: no unintentional adjustment
- box-joint design: high stability due to double guide
- self-locking on pipes and nuts: power-saving operation and no slipping off the workpiece
- gripping surfaces with special hardened teeth: wear resistant
- guard: prevents "knuckle-busting"
- favorable lever action: optimum power transmission
- forged from Chrome-Vanadium Electric Steel, oil-hardened: high load capacity
- **Cobra...matic:** with spring adjusted action for instant adjustment
- **Cobra ES:** particularly good access to the workpiece due to very slim construction of head and joint area

Your distributor



KNIPEX-Werk
C. Gustav Putsch KG

Oberkamper Strasse 13
42349 Wuppertal (Germany)





Tel.: +49 (0) 202 – 47 94-0
Fax: +49 (0) 202 – 47 74 94

info@knipex.de
www.knipex.de

The 150 mm Pliers Wrench.



The small professional tool with the quality and functional features of the large pliers wrenches.

Article-No.	EAN 4003773-	Working capacities		 mm	Adjustment positions	 mm	 g
86 03 150	069676	head nickel plated, plastic coated handles	1"	27	14	150	175
86 05 150	069928	head nickel plated, with two-colour dual component handles	1"	27	14	150	195



Your distributor



KNIPEX-Werk
C. Gustav Putsch KG
 Oberkamper Strasse 13
 42349 Wuppertal (Germany)
 Tel.: +49 (0) 202 – 47 94-0
 Fax: +49 (0) 202 – 47 74 94
 info@knipex.de
 www.knipex.de

L100 01991/0103.09/3.000/EN Printed in Germany.

The Original in Pocket Size.



The 150 mm Pliers Wrench.



- ▶ heavy-duty, small professional tool for precision tightening work
- ▶ same quality and functional features as the large pliers wrenches
- ▶ gripping of all widths across flats up to 27 mm
- ▶ 14 adjustment positions for comfortable handling



KNIPEX Quality – Made in Germany

The 150 mm Pliers Wrench – for tightening, bending, pressing, holding.



The solution for fine mechanical work: the mini pliers wrench adjust to suit the smallest workpieces – simply by pushing a button!

By secure locking the smooth jaws of the 150 mm pliers wrench prevent damage to sensitive surfaces – like the large pliers wrenches do.

The optimised handle position and a 10 : 1 ratio of hand force provide excellent results.

Applications

- **in industry and various trades**
e. g. tightening, bending, pressing, holding
- **in sport and leisure**
e. g. emergency tool kit/boats, diving, bicycles and motorcycles
- **in hobbies and DIY work**
e. g. model construction, bonded joints, closing chain links
- **in the home and garden**
e. g. fittings, furniture assembly, garden tools, moving home

Original KNIPEX Pliers Wrench in pocket size.



86 05 150
Illustration 1:1

Light, reliable and efficient work:
14 adjustment positions for ergonomic handle position and different workpiece sizes.



- excellent for gripping, holding, pressing and bending workpieces
- zero-backlash surface pressure of parallel jaws prevents damage to sensitive components
- fast adjustment directly on the workpiece by pushing a button
- no unintentional shift of the gripping jaw position, no slipping of the joint
- ratchet-action gripping jaws allow fast tightening and releasing
- cam action provides a 10 : 1 ratio for strong gripping power



Universal Mini Pliers Wrench for tightening, bending, pressing and holding.

