

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301360057

Status:

Active

Overview:

Outlet Boxes

Description:

Super-Safeway Multi-Tap (3) Non-NEMA 20A/125V/250V Outlet Box with Buss Bars, 15.24m (50.0') Cord Length, 14/3 SOW Cord, Non-NEMA 20A/125V/250V Plug



Series image - Reference only

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                             |
|-------------------------------|-----------------------------|
| Agency Certification          |                             |
| CSA                           | LR6837                      |
| General                       |                             |
| Product Family                | Power Distribution          |
| Series                        | 130136                      |
| Enclosure Rating              | N/A                         |
| GFCI Reset                    | N/A                         |
| Mounting Style                | Portable                    |
| Open Neutral Relay            | N/A                         |
| Overview                      | Outlet Boxes                |
| Product Name                  | Super-Safeway               |
| Receptacle Type               | Triple                      |
| Type                          | Multi-Tap and Strip Cordset |
| UPC                           | 78678875663                 |
| Physical                      |                             |
| Cord Diameter                 | 13.59mm (.535")             |
| Cord Grip Body Size           | Double C-Clamp              |
| Cord Length                   | 15.24m (50.0')              |
| Feed-Thru                     | No                          |
| Flip Lid                      | No                          |
| Material - Housing            | Rubber                      |
| Number of Receptacles         | 3                           |
| Packaging Type                | Carton                      |
| Electrical                    |                             |
| Cord Type                     | 14/3 SOOW                   |
| Current - Maximum per Contact | 20.0A                       |
| GFCI                          | No                          |
| Ground Continuity Monitor     | No                          |
| NEMA Configuration            | Non-NEMA                    |
| Voltage - Maximum             | 120V                        |
| Material Info                 |                             |
| Engineering Number            | 32708B143                   |

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

130136 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION