











9000 SERIES - MINIATURE MOMENTARY PUSHBUTTON SWITCHES

OPTION DRAWINGS & SPECIAL OPTIONS

CAPS Note: replace last '0' in p/n with color code. (order separately)

 3.00 (.118) 5.00 DIA (.195) 4.00 (.157)	 3.00 (.118) 6.00 DIA (.234 DIA) 6.35 (.250)	 3.00 (.118) 9.40 DIA (.370) 6.35 (.250)	 3.00 (.118) 10.00 DIA (.395) 7.50 (.295)																			
U900	U1140	U1720	U480 Standard																			
 5.00 (.118) 15.00 DIA (.590 DIA) 6.00 (.235)	 3.00 (.118) 11.50x11.50 (.452 SQ) 4.00 (.157)	 3.00 (.118) 11.50x11.50 (.452 SQ) 6.00 (.235)		<table><tr><th colspan="2">Colors</th></tr><tr><td>1</td><td>blue</td></tr><tr><td>2</td><td>black</td></tr><tr><td>3</td><td>green</td></tr><tr><td>4</td><td>gray</td></tr><tr><td>5</td><td>yellow</td></tr><tr><td>6</td><td>red</td></tr><tr><td>7/1</td><td>white</td></tr><tr><td>9</td><td>orange</td></tr></table>	Colors		1	blue	2	black	3	green	4	gray	5	yellow	6	red	7/1	white	9	orange
Colors																						
1	blue																					
2	black																					
3	green																					
4	gray																					
5	yellow																					
6	red																					
7/1	white																					
9	orange																					
U630	U2430 Square	U2020 Square																				

DRESS NUTS Chrome plated. Order separately.

 U1636 (for cap U1140)	 U825 (for cap U630)	 U840 (for cap U480)
--	--	---

SPECIAL OPTIONS

F Tin plated terminals (for p.c. terminals only).

X601 Silver plated brass contacts
 Contact ratings: 0.2A 250VAC, 0.4A 125VAC or 0.5A 30VDC
 Electric life: 20,000 cycles minimum.
 Minimum quantity: 5,000 pieces.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

C