

5

4

3

2

1

D

C

B

A



Description: Stright BNC Crimp Plug For RG6 Cable

Part No: CPMC885

Application: For Cable RG-6

Crimp Tool: 24-8856P

Impedance: 50 Ohms

Fequency Range: 0-4 GHz

Material:

Body	Zinc	Nickel plated
Contact	Brass	Gold plated
Insulator	PTFE	
Crimp Sleeve	Brass	Nickel plated
Coupling Nut	Zinc	Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000




DRAWING NO. CPMC885-CUST									
REVISIONS									
01	OFFICAL RELEASE								
	03-05-09	Z	G	B	Y	T			Thomas Chow

D

C

B

A



DIM OUTLINE

CUSTOMER COPY

受控 CONTROLLED DOCUMENT				
编号 P/N	CPMC885-CUST	版本 Rev	01	日期 Rel'd Date Apr29,09

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY GARY.ZHG	DATE 03-05-09
DECIMALS	mm	CHECKED BY TERRY.W	DATE 03-05-09
X	± 0.5	APPROVED BY THOMAS	DATE 03-10-09
X.X	± 0.3		
X.XX	± 0.1		
ANGLES	± 0.5°	U/M mm	

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 Connectivity Solutions	
TITLE STRAIGHT BNC CRIMP PLUG FOR RG6 CABLE	

SHEET 1 OF 1	DRAWING NO. CPMC885-CUST	SIZE A
-----------------	-----------------------------	-----------

5

4

3

2

1