


Transformer No.	AA 23963	1 -Phase / -con. 50 Hz.
Customer	HEWLETT-PACKARD	Note
Assembly comp.	CENTER POTTED + METAL DISK	Date/sign. 01-21-1994 JAKOB 



Marking



MADE BY AMVECO MAGNETICS USA TRF # AA 23963
 HP P/N 9100-5134
 PRIM. 0-100-120V 0-120V 50/60Hz 66VA
 SEC. 37.6V 1.6A





(HIQ266)

Changed from
 AA 23212B
 Changed to

Tests.		Uo. Tolerance, $\pm$ 3 %		Iomax 21.3 (mA)	103.4 V over P1.	Isol: 4K v
Dimensions:		Max H: 1.575" (inch)		Max. ϕ : 4.33" (inch)	Terminals: PRIM 110 mm SEC 280 mm	

LEAD LENGTHS ARE MEASURED TO THE END OF THE CONNECTORS



1 PC METAL DISK ϕ 90 mm (w/ SPECIAL DIMPLE)
 2 PCS RUBBER GASKETS ϕ 90 mm

CENTER POTTED WITH 0.25" HOLE DRILLED

MOLEX CONNECTORS

Shipping Weight: 2.4 lbst

D.O. 1/15/01