

KEY PRODUCT SELECTOR GUIDE

KEY PRODUCT SELECTOR GUIDE

NEMA CONFIGURATION	VOLTAGE/AMPERAGE	PAGE	WATERTITE®					
			PLUG	CONNECTOR	SINGLE FLIP LID w/ FEMALE RECEPTACLE	DUPLEX FLIP LID w/ FEMALE RECEPTACLE	SINGLE FLIP LID w/ MALE RECEPTACLE	CONNECTOR FOR MALE RECEPTACLE
2-POLE/2-WIRE								
1-15	15A/125V	50-53	14W04 14W19¹	15W04	60W04	60W04DPLX	59W04	15W04MB
L1-15	15A/125V	50-53	24W04	25W04	65W04	65W04DPLX	64W04	25W04MB
L2-20	20A/250V	70-73	26W07	27W07	67W07	67W07DPLX	66W07	27W07MB
2-POLE/3-WIRE								
5-15	15A/125V	54-61	14W47	15W47	60W47	60W47DPLX	59W47	15W47MB
L5-15	15A/125V	54-61	24W47	25W47	65W47	65W47DPLX	64W47	25W47MB
6-15	15A/250V	62-65	14W49	15W49	60W49	60W49DPLX	59W49	15W49MB
L6-15	15A/250V	62-65	24W49	25W49	65W49	65W49DPLX	64W49	25W49MB
7-15	15A/277V	62-65	14W34	15W34	60W34	60W34DPLX	59W34	15W34MB
L7-15	15A/277V	62-65	24W34	25W34	65W34	65W34DPLX	64W34	25W34MB
5-20	20A/125V	74-81	14W33	15W33	60W33	60W33DPLX	59W33	15W33MB
L5-20	20A/125V	74-81	26W47	27W47	67W47	—	66W47	27W47MB
6-20	20A/250V	74-75, 78-81	14W48	15W48	60W48	60W48DPLX	59W48	15W48MB
L6-20	20A/250V	74-75, 78-81	26W48	27W48	67W48	—	66W48	27W48MB
L7-20	20A/277V	74-75, 78-81	26W49	27W49	67W49	—	66W49	27W49MB
L5-30	30A/125V	98-101	28W47	29W47	69W47	—	68W47	29W47MB
L6-30	30A/250V	98-101	28W48	29W48	69W48	—	68W48	29W48MB
L7-30	30A/277V	98-101	28W49	29W49	69W49	—	68W49	29W49MB
6-50	50A/250V	118	—	—	—	—	—	—
Non-NEMA Locking CA	50A/125V	118-121	CS63W61	CS63W60	CS69W60	—	—	—
Non-NEMA Locking	50A/125V	118-121	63W61	63W60	69W60	—	—	—
Non-NEMA Locking CA	50A/250V	118-121	CS82W65	CS82W64	69W64	—	—	—
Non-NEMA Locking	50A/600VAC/250VDC	118-121	37W63	37W62	69W62	—	—	—
Non-NEMA Locking CA	50A/480V	118-121	CS84W65	CS84W64	67W64	—	—	—
3-POLE/3-WIRE								
Non-NEMA	15A/125V 10A/250V	66-69	14W07	60W07DPLX	15W07	60W07	59W07	15W07MB
Non-NEMA Locking	15A/125V 10A/250V	66-69	24W07	65W07DPLX	25W07	65W07	64W07	25W07MB
Non-NEMA Locking	20A/125V/250V	82-85	26W08	27W08	—	67W08	66W08	27W08MB
Non-NEMA Locking	20A/250V GRNDING TAB	82-85	26W08G	27W08G	—	—	—	27W08GMB
Non-NEMA Locking	30A/125V/250V	102-105	28W08	29W08	—	69W08	68W08	29W08MB
3-POLE/4-WIRE								
L14-20	20A/125V/250V	86-89	26W74	27W74	67W74	—	66W74	27W74MB
L15-20	20A/250V/3ø	90-93	26W75	27W75	67W75	—	66W75	27W75MB
L16-20	20A/480V/3ø	90-93	26W76	27W76	67W76	—	66W76	27W76MB
L14-30	30A/125V/250V	106-109	28W74	29W74	69W74	—	68W74	29W74MB
L15-30	30A/250V/3ø	110-113	28W75	29W75	69W75	—	68W75	29W75MB
L16-30	30A/480V/3ø	110-113	28W76	29W76	69W76	—	68W76	29W76MB
L17-30	30A/600V/3ø	110-113	28W77	29W77	69W77	—	68W77	29W77MB
Non-NEMA Locking CA	50A/125V/250V	120-121	CS63W65	CS63W64	CS60W64	—	—	—
Non-NEMA Locking	50A/125V/250V	120-121	63W65	63W64	60W64	—	—	—
Non-NEMA Locking CA	50A/250V/3ø	120-121	CS83W65	CS83W64	65W64	—	—	—
Non-NEMA Locking	50A/600VAC/250VDC	120-121	37W65	37W64	66W64	—	—	—
Non-NEMA Locking CA	50A/480V/3ø	120-121	CS81W65	CS81W64	64W64	—	—	—
4-POLE/4-WIRE								
Non-NEMA Locking	20A/120V/208V	82-85	26W09	27W09	67W09	—	66W09	27W09MB
Non-NEMA Locking	30A/120V/208V	102-105	28W09	29W09	69W09	—	68W09	29W09MB
4-POLE/5-WIRE								
L21-20	20A/120V/208V/3øY	94-97	26W81	27W81	67W81	—	66W81	27W81MB
Non-NEMA Locking	20A/250V 10A/600V	82-85	26W10	27W10	67W10	—	66W10	27W10MB
L22-20	20A/227V/480V/3øY	94-97	26W82	27W82	67W82	—	66W82	27W82MB
L23-20	20A/347V/600V/3øY	94-97	26W83	27W83	67W83	—	66W83	27W83MB
L21-30	30A/120V/208V/3øY	114-117	28W81	29W81	69W81	—	68W81	29W81MB
L22-30	30A/277V/480V/3øY	114-117	28W82	29W82	69W82	—	68W82	29W82MB
L23-30	30A/347V/600V/3øY	114-117	28W83	29W83	69W83	—	68W83	29W83MB

¹ POLARIZED

NEMA CONFIGURATION	VOLTAGE/AMPERAGE	PAGE	SUPER-SAFEWAY®		SAFEWAY®			
			PLUG	CONNECTOR	PLUG	CONNECTOR	FLANGED INLET	FLANGED RECEPTACLES
2-POLE/2-WIRE								
1-15	15A/125V	50-53	1404 1419¹	1504	5166 5176¹	5169	1404MB	1504MB
L1-15	15A/125V	50-53	2404	2504	24T04	25T04	2404MB	2504MB
L2-20	20A/250V	70-73	2607	2707	26T07	27T07	2607MB	2707MB
2-POLE/3-WIRE								
5-15	15A/125V	54-61	1447	1547	5266	5269	1447MB	1547MB
L5-15	15A/125V	54-61	2447	2547	4720	4729	2447MB	2547MB
6-15	15A/250V	62-65	1449	1549	5666	5669	1449MB	1549MB
L6-15	15A/250V	62-65	2449	2549	24T49	25T49	2449MB	2549MB
7-15	15A/277V	62-65	1434	1534	5766	5769	1434MB	1534MB
L7-15	15A/277V	62-65	2434	2534	4770	4779	2434MB	2534MB
5-20	20A/125V	74-81	1433	1533	5366	5369	1433MB	1533MB
L5-20	20A/125V	74-81	2647	2747	26T47	27T47	2647MB	2747MB
6-20	20A/250V	74-75, 78-81	1448	1548	5466	5469	1448MB	1548MB
L6-20	20A/250V	74-75, 78-81	2648	2748	26T48	27T48	2648MB	2748MB
L7-20	20A/277V	74-75, 78-81	2649	2749	26T49	27T49	2649MB	2749MB
L5-30	30A/125V	98-101	2847	2947	28T47	29T47	2847MB	2947MB
L6-30	30A/250V	98-101	2848	2948	28T48	29T48	2848MB	2948MB
L7-30	30A/277V	98-101	2849	2949	28T49	29T49	2849MB	2949MB
6-50	50A/250V	118	8664	8665	—	—	—	—
Non-NEMA Locking CA	50A/125V	118-121	—	—	CS6361N	CS6360N	CS6377	CS6370²
Non-NEMA Locking	50A/125V	118-121	—	—	6361CRN	6360CRN	6377CR	6370CR²
Non-NEMA Locking CA	50A/250V	118-121	—	—	CS8265N	CS8264N	CS8275	CS8269²
Non-NEMA Locking	50A/600VAC/250VDC	118-121	—	—	3763N	3762N	3777	3771²
Non-NEMA Locking CA	50A/480V	118-121	—	—	CS8465N	CS8464N	CS8475	CS8469²
3-POLE/3-WIRE								
Non-NEMA	15A/125V 10A/250V	66-69	1407	1507	5276	1507	1407MB	1507MB
Non-NEMA Locking	15A/125V 10A/250V	66-69	2407	2507	4730	4739	2407MB	2507MB
Non-NEMA Locking	20A/125V/250V	82-85	2608	2708	26T08	27T08	2608MB	2708MB
Non-NEMA Locking	20A/250V GRNDING TAB	82-85	2608G	2708G	26T08G	27T08G	—	—
Non-NEMA Locking	30A/125V/250V	102-105	2808	2908	28T08	29T08	2808MB	2908MB
3-POLE/4-WIRE								
L14-20	20A/125V/250V	86-89	2674	2774	26T74	27T74	2674MB	2774MB
L15-20	20A/250V/3ø	90-93	2675	2775	26T75	27T75	2675MB	2775MB
L16-20	20A/480V/3ø	90-93	2676	2776	26T76	27T76	2676MB	2776MB
L14-30	30A/125V/250V	106-109	2874	2974	28T74	29T74	2874MB	2974MB
L15-30	30A/250V/3ø	110-113	2875	2975	28T75	29T75	2875MB	2975MB
L16-30	30A/480V/3ø	110-113	2876	2976	28T76	29T76	2876MB	2976MB
L17-30	30A/600V/3ø	110-113	2877	2977	28T77	29T77	2877MB	2977MB
Non-NEMA Locking CA	50A/125V/250V	120-121	—	—	CS8365N	CS8364N	CS8375	CS8369²
Non-NEMA Locking	50A/125V/250V	120-121	—	—	6365CRN	6364CRN	6375CR	6369CR²
Non-NEMA Locking CA	50A/250V/3ø	120-121	—	—	CS8365N	CS8364N	CS8375	CS8369²
Non-NEMA Locking	50A/600VAC/250VDC	120-121	—	—	3765N	3764N	3775	3769²
Non-NEMA Locking CA	50A/480V/3ø	120-121	—	—	CS8165N	CS8164N	CS8175	CS8169²
4-POLE/4-WIRE								
Non-NEMA Locking	20A/120V/208V	82-85	2609	2709	26T09	27T09	2609MB	2709MB
Non-NEMA Locking	30A/120V/208V	102-105	2809	2909	28T09	29T09	2809MB	2909MB
4-POLE/5-WIRE								
L21-20	20A/120V/208V/3øY	94-97	2681	2781	26T81	27T81	2681MB	2781MB
Non-NEMA Locking	20A/250V 10A/600V	82-85	2610	2710	26T10	27T10	2610MB	2710MB
L22-20	20A/227V/480V/3øY	94-97	2682	2782	24T04	25T04	2607MB	2707MB
L23-20	20A/347V/600V/3øY	94-97	2683	2783	26T83	27T83	2683MB	2783MB
L21-30	30A/120V/208V/3øY	114-117	2881	2981	28T81	29T81	2881MB	2981MB
L22-30	30A/277V/480V/3øY	114-117	2882	2982	28T82	29T82	2882MB	2982MB
L23-30	30A/347V/600V/3øY	114-117	2883	2983	28T83	29T83	2607MB	2707MB

¹ POLARIZED

² SINGLE RECEPTACLES AND NOT FLANGED RECEPTACLES