


Distributed by:






www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 315388

Rating	6A 125V AC / 3A 250V AC	Mount Hole	Circuit Structure
Contact R	50m ohm Max.		
Insulation R	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Circuit	2P SPST ON-OFF		
Operating Temperature	-20°C~65°C		



DCC. NO.

A4 DRAWING NO.

MATERIAL

DRWN Simon Yeh DATE 2009.07.16
 CHK DATE
 APVD DATE

GOLDSUN ELECTRONICS CO., LTD.
PUNKTAL INDUSTRIAL CO., LTD.

PART NAME

Rev.

1

PART NO.

315388

MODEL

UNIT: mm

SCALE:

SHEET 1 OF 1

CAS No:
ERN No: