

NSUV365 / NSUV395

PROFESSIONAL ULTRA VIOLET FLASHLIGHT RANGE

SPECIFICATION

Wavelength	395 nm
Running time	3.5 / 6 hours
Battery	2x CR123A batteries (not included)
Product size (mm)	1W UV LED
Product weight (kg)	L132 x Dia. 33.5
Boxed weight (kg)	0.144 (inc. batteries)
Box size (mm)	L160 x W38 x H38
Part no.	NSUVLED395

NSUV395



This compact and lightweight flashlight utilises the latest in UV technology. With a 1W powerful LED emitting an Ultra Violet beam. This product is designed specifically for Forensic Applications and Crime Investigation. Manufactured in durable aluminum casing, it is water and shock resistant.

- 1W High Powered UV LED
- 2 x CR123A batteries (not included)
- Running Time 3.5 hours / 6 hours
- Wavelength 390 -395nm
- Designed for Forensic Applications
- Durable Aluminium Casing
- Water and Shock Resistant
- Tail Cap Tactical Switch
- Length 132mm, Head Dia. 33.5mm
- Weight 144g (inc. batteries)

SPECIFICATION

Wavelength	365nm
Running time	4 hours
Battery	18650 Lithium
Light source	5W UV LED 365NM
Product size (mm)	L153 x Dia. 40
Product weight (kg)	0.185 (inc batteries)
Box size (mm)	L186 x W160 x H87
Part no.	NSUVLED365

NSUV365

RECHARGEABLE



This compact and lightweight flashlight utilises the latest in UV technology. With a 5W powerful LED emitting an Ultra Violet beam, covering up to 35m. This product is designed specifically for Forensic Applications and Crime Investigation. Manufactured in durable aluminum casing, it is water and shock resistant. This product comes complete with, two rechargeable batteries, mains and vehicle charger.

- 5W UV LED - Class 1M Laser
- Wavelength 365 nm
- 35m beam, without dark spots or rings
- Rechargeable 18650 Lithium battery
- Tail Cap Tactical Switch
- Designed for forensic applications
- Fibre and body fluid search
- Durable aluminium casing
- Water and shock resistant
- Can be powered by standard CR123A batteries

Mains Charger



Vehicle Charger

