


SERIES 62C Concentric Shaft

FEATURES

- Economical Size
- Combined Functionality
- Optically Coupled for more than a Million Cycles of Operations
- Optional Integral Pushbutton
- Compatible with CMOS, TTL, and HCMOS Logic
- Available with 12, 16, 24, and 32 Detent Positions for Deck
- Choices of Cable Length and Terminations
- Available in 3.3 Volt Input (contact Grayhill for details)

APPLICATIONS

- Used to Set Radio Frequency, Drill Depth, RPM, Menu Selection, Parameter Selection for Patient Monitoring Devices, etc.





DIMENSIONS in inches (and millimeters)


Unless otherwise specified, standard tolerance are:

Linear $\pm .025$
Diameter $\pm .010$
Angle $\pm 2.0^\circ$

Deck A: 0.250 (6,35) shaft
Deck B: 0.125 (3,18) shaft



CIRCUITRY, TRUTH TABLE AND WAVEFORM: Standard Quadrature 2-Bit Code



SPECIFICATIONS

Pushbutton Switch Ratings

Rating: 5 Vdc, 10 mA, resistive**Contact Resistance:** less than 10 ohms (TTL or CMOS compatible)**Voltage Breakdown:** 250 Vac between mutually insulated parts**Contact Bounce:** less than 4 mS at make, less than 10 mS at break**Actuation Life:** 3,000,000 operations**Actuation Force:** 1000 $\pm$ 300 grams**Pushbutton Travel:** .010 / .025 inch

Encoder Ratings

Coding: 2-bit quadrature coded output**Operating Voltage:** 5 $\pm$.25 Vdc**Supply Current:** 50 mA maximum at 5 Vdc**Logic High:** 3.8V minimum**Logic Low:** 0.8V maximum**Logic Rise and Fall Times:** less than 30 mS**Operating Torque:** 2.0 in-oz $\pm$ 1.4 in-oz initially**Rotational Life:** more than 1,000,000 cycles of operation (1 cycle = 360° rotation)**Shaft Push Out Force:** 45 lbs minimum**Mounting Torque:** 15 in-lbs maximum**Operating Speed:** 100 RPM maximum**Axial Shaft Play:** 0.010 max. for each shaft


Environmental Ratings

Operating Temp. Range: -40°C to 85°C**Storage Temp. Range:** -55°C to 100°C**Relative Humidity:** 90–95% at 40°C, 96 hrs.**Vibration Resistance:** Harmonic motion with amplitude of 15g, within a varied 10 to 2000 Hz frequency for 12 hours per MIL-STD-202, Method 204**Shock Resistance:** Test 1: Tested at 100g for 6 mS, half sine, 12.3 ft/s Test 2: 100g for 6 mS, sawtooth, 9.7 ft/s

Materials and Finishes

Bushing: Zinc casting**Shaft:** Aluminum**Shaft Retaining Ring:** Stainless steel**Detent Spring:** Stainless steel**Printed Circuit Board:** NEMA grade FR-4**Terminals:** Brass, tin-plated**Mounting Hardware:** One brass, nickel-plated nut and zinc-plated spring steel with clear trivalent chromate finish lockwasher supplied with each switch. (Nut is 0.094 inches thick by 0.433 inches across flats)**Rotor:** Thermoplastic**Code Housing:** Reinforced thermoplastic**Pushbutton Dome:** Stainless steel**Pushbutton Housing:** Thermoplastic**Pushbutton Contact:** Brass, nickel-plated**Dome Retaining Disk:** Thermoplastic**Strain Relief:** Stainless steel**Cable:** 28 AWG, stranded/top coated wire, PVC coated on .050 centers (cable version)**Header Pins:** Phosphor bronze, tin-plated**Insulator:** Glass-filled polyester**Spacer:** Zinc casting

ORDERING INFORMATION



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Grayhill:

[62C1111-02-040C](#) [62C1111-02-060C](#) [62C1111-02-P](#) [62C2211-02-020S](#) [62C2222-02-P](#) [62C1111-01-100C](#)
[62C1515-01-020C](#) [62C1522-01-040C](#) [62C2222-01-035C](#) [62C2222-01-080C](#) [62C1515-02-020C](#) [62C2211-01-060C](#)
[62C1111-01-060S](#) [62C3011-02-060C](#) [62C2230-01-020C](#) [62C1111-02-060S](#) [62C1111-02-250S](#) [62C1111-02-040S](#)
[62C2222-01-120S](#) [62C3030-01-060S](#) [62C2211-02-P](#) [62C2222-01-P](#) [62C2215-02-035S](#) [62C2215-02-080S](#)
[62C1515-01-040S](#) [62C2211-02-040C](#) [62C1122-01-020C](#) [62C2230-02-040C](#) [62C2222-02-100C](#) [62C1111-01-020C](#)
[62C3030-01-P](#) [62C1111-01-120S](#) [62C2222-02-060S](#) [62C2222-02-100S](#) [62C2222-02-030C](#) [62C1111-02-090C](#)
[62C2222-01-125C](#) [62C1515-02-040S](#) [62C1111-02-070C](#) [62C2230-01-040C](#) [62C1522-02-100C](#) [62C1515-01-035C](#)
[62C2215-02-P](#) [62C1530-02-P](#) [62C2222-01-050C](#) [62C1515-01-050C](#) [62C1515-01-080S](#) [62C1122-01-060C](#)
[62C2211-02-060C](#) [62C2222-02-020C](#) [62C1511-01-020S](#) [62C2222-01-060C](#) [62C1111-02-090S](#) [62C3011-01-020C](#)
[62C1111-02-075S](#) [62C1515-02-060C](#) [62C2222-01-250C](#) [62C1111-02-030S](#) [62C2222-02-250C](#) [62C2211-01-P](#)
[62C2222-01-025C](#) [62C2215-02-060S](#) [62C3030-02-P](#) [62C2222-01-040C](#) [62C2215-01-040C](#) [62C1111-01-030C](#)
[62C2222-02-040C](#) [62C2211-01-040C](#) [62C3011-01-040S](#) [62C1111-01-060C](#) [62C1111-02-120C](#) [62C2211-02-100S](#)
[62C1515-02-P](#) [62C3011-02-040C](#) [62C1518-01-020S](#) [62C1511-02-020S](#) [62C1111-02-100C](#) [62C1515-01-P](#)
[62C2211-02-035S](#) [62C2222-02-080S](#) [62C1111-02-250C](#) [62C2230-01-060C](#) [62C1122-01-P](#) [62C2222-02-020S](#)
[62C3030-02-020C](#) [62C1515-01-100S](#) [62C1111-02-050S](#) [62C2211-02-060S](#) [62C2222-02-120S](#) [62C2222-01-060S](#)
[62C3030-02-040S](#) [62C2222-01-120C](#) [62C1515-02-035C](#) [62C2222-01-035S](#) [62C1515-02-020S](#) [62C3022-02-P](#)
[62C1522-01-100C](#) [62C2230-02-P](#) [62C2215-02-060C](#) [62C3030-02-060S](#)