



Sample photo

Order symbol: CAB ABS 302018 T3B
Product nbr: 8183032
Description: Cabinet, ABS
Remarks: Lock on the long side

EAN: 6418074020116
El. number:
 Finland 3424355
 Denmark 8212019014
 Italy 7812020
 Sweden 2540035

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		L	W	H	Rating:
mm:		300	200	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	7.9	7.1	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 50298 1998
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
EKIV 23		Mounting plate			
EKIV 17		DIN-35 Mounting rail			
EKIV 27		DIN-35 Mounting rail			
FP A 23		Swing-out door, aluminium			
FP 23		Front plate			
FP 12-23		Front Plate			
DRF 23		DIN rail frame set			
DRF 33		DIN rail frame set			

