


# LAMINATED TRANSFORMERS

Type EI30 / 15.5 - 2.0VA




- Frequency 50/60Hz
- Potted under vacuum
- Split-bobbin
- Temperature class ta 70°C/B
- VDE rated as inherently short-circuit proof
- Weight: 0.10kg
- Packaging unit: 25 pieces (tube)

## Mechanical



## Schematics



| Primary (V) | Secondary (V / mA) | No-Load Voltage (V) | Schematic No. | Part Number | Agency Approvals |
|-------------|--------------------|---------------------|---------------|-------------|------------------|
| 230         | 6 / 333            | 10.50               | 1             | 030-7304.0  | 1/3*             |
| 230         | 9 / 222            | 14.60               | 1             | 030-7305.0  | 1/3*             |
| 230         | 12 / 166           | 20.00               | 1             | 030-7306.0  | 1/3*             |
| 230         | 15 / 133           | 26.00               | 1             | 030-7307.0  | 1/3*             |
| 230         | 18 / 111           | 29.60               | 1             | 030-7308.0  | 1/3*             |
| 230         | 24 / 83            | 37.20               | 1             | 030-7309.0  | 1/3*             |
| 230         | 2x6 / 166          | 2x8.70              | 2             | 030-7310.0  | 1/3*             |
| 230         | 2x9 / 111          | 2x14.60             | 2             | 030-7311.0  | 1/3*             |
| 230         | 2x12 / 83          | 2x19.45             | 2             | 030-7312.0  | 1/3*             |
| 230         | 2x15 / 66          | 2x24.10             | 2             | 030-7313.0  | 1/3*             |
| 230         | 2x18 / 55          | 2x29.10             | 2             | 030-7314.0  | 1                |
| 230         | 2x24 / 42          | 2x36.50             | 2             | 030-7315.0  | 1                |
| 115         | 6 / 333            | 10.50               | 1             | 030-7292.0  | 1/3*             |
| 115         | 9 / 222            | 14.60               | 1             | 030-7293.0  | 1/3*             |
| 115         | 12 / 166           | 20.00               | 1             | 030-7294.0  | 1/3*             |
| 115         | 15 / 133           | 26.00               | 1             | 030-7295.0  | 1/3*             |
| 115         | 18 / 111           | 29.60               | 1             | 030-7296.0  | 1/3*             |
| 115         | 24 / 83            | 37.20               | 1             | 030-7297.0  | 1/3*             |
| 115         | 2x6 / 166          | 2x8.70              | 2             | 030-7298.0  | 1/3*             |
| 115         | 2x9 / 111          | 2x14.60             | 2             | 030-7299.0  | 1/3*             |
| 115         | 2x12 / 83          | 2x19.45             | 2             | 030-7300.0  | 1/3*             |
| 115         | 2x15 / 66          | 2x24.10             | 2             | 030-7301.0  | 1/3*             |
| 115         | 2x18 / 55          | 2x29.10             | 2             | 030-7302.0  | 1                |
| 115         | 2x24 / 42          | 2x36.50             | 2             | 030-7303.0  | 1                |
| 2x115       | 6 / 333            | 10.50               | 3             | 030-6429.0  | 1/3*             |
| 2x115       | 9 / 222            | 14.60               | 3             | 030-6432.0  | 1/3*             |
| 2x115       | 12 / 166           | 20.00               | 3             | 030-6435.0  | 1/3*             |
| 2x115       | 15 / 133           | 26.00               | 3             | 030-6438.0  | 1/3*             |
| 2x115       | 18 / 111           | 29.60               | 3             | 030-6441.0  | 1/3*             |
| 2x115       | 24 / 83            | 37.20               | 3             | 030-6447.0  | 1/3*             |
| 2x115       | 2x6 / 166          | 2x8.70              | 4             | 030-6452.0  | 1/3*             |
| 2x115       | 2x9 / 111          | 2x14.60             | 4             | 030-6455.0  | 1/3*             |
| 2x115       | 2x12 / 83          | 2x19.45             | 4             | 030-6458.0  | 1/3*             |
| 2x115       | 2x15 / 66          | 2x24.10             | 4             | 030-6461.0  | 1/3*             |
| 2x115       | 2x18 / 55          | 2x29.10             | 4             | 030-6464.0  | 1                |
| 2x115       | 2x24 / 42          | 2x36.50             | 4             | 030-6470.0  | 1                |

\*NOTE: When checking the approval status of this product with VDE, add the prefix "BV" and the suffix "S" to the orderable Part Number (these letters will also be found on the part label). The prefix and suffix are not part of the orderable Part Number.