





REV.	DATE	DESCRIPTION
NC	08/05/99	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connex Connector Corporation			
1 BODY/BARREL	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN G.R.S.	08/05/99				
2 INSULATOR	TEFLON	NATURAL		CHECKED					
3 CONTACT PIN	BRASS	GOLD		ISSUED					
4 FERRULE	COPPER	NICKEL							
5 HEAT SHRINK TUBE									
6						TITLE	SMB R/A CRIMP JACK (FOR RG-174/U, 188A/U, 316/U CABLE)		
7						SIZE	FSCM NO.	DWG. NO.	REV.
8						A	99001	142251.DWG	NC
DO NOT SCALE DRAWING				SCALE	NA	PART NO.	142251	SHEET	1 OF 1