

REDINGTON COUNTERS, INC.
P.O. Box 608, 130 Addison Road, Windsor, CT 06095
Toll Free: (860) 688-6205 • Fax: 860/688-1591
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # P8-1027, 24VDC, panel mount, lock and key reset



24VDC, panel mount, lock and key reset

A 6 figure general purpose, rugged, electromechanical counter, either panel or base mounted, with manual knob reset, key reset, or non-reset. Frame and housing provides rigid support for accurate alignment and trouble-free use. Distinctive numerals enhance visibility under adverse viewing conditions.

SPECIFICATIONS

Model No.	10
Mounting	Panel Mount
Display	7 Figures, white on black, 0.19 inch (5mm) high
Display Height	0.19 Inch
Display Height	5 mm
No. of Digits	7
Voltage	24 VAC
Tolerance- Voltage	±177 10%, but not to exceed 10 volts
Power	7.8 watts (nominal)
Reset Type	Lock and key
Speed	1000 counts/minute (min. 30ms - on, 30ms - off)
Operating Temperature	-15 to +140 °F
Operating Temperature	-26 to +60 °C
Approvals	UL Recognized, CSA Certified, CE Compliant
Termination	(2) No. 22 AWG 105°C wire leads, 8 inch (203mm) long
Weight	14 to 18 oz
Weight	397 to 510 gm
Operating Life	Beyond 50 million counts
Stock Availability	No
Panel Cutout	4.88 x 1.75 Inch
Panel Cutout	124.0 x 44.5 mm

