

## Screw plug


10xx M/G

### Configuration

|                   |                                |
|-------------------|--------------------------------|
| Screw plug        | Brass CuZn39Pb3, nickel-plated |
| O-ring            | Nitrile rubber                 |
| Connecting thread | Pg as per DIN 40430            |

### Properties

|                   |                                                                                                                           |
|-------------------|---------------------------------------------------------------------------------------------------------------------------|
| Temperature range | <ul style="list-style-type: none"> <li>for secure sealing of unused threaded or clearance hole</li> </ul> -30°C<br>+100°C |
| Protection grade  | IP68                                                                                                                      |



### Features

round

| A       | L   | H  | Da |  | Part No. |
|---------|-----|----|----|-------------------------------------------------------------------------------------|----------|
|         | mm  | mm | mm | Piece                                                                               |          |
| Pg 7    | 4,5 | 7  | 16 | 100                                                                                 | 1007 M/G |
| Pg 9    | 4,5 | 8  | 19 | 100                                                                                 | 1009 M/G |
| Pg 11   | 4,5 | 8  | 22 | 100                                                                                 | 1011 M/G |
| Pg 13,5 | 6   | 10 | 24 | 100                                                                                 | 1013 M/G |
| Pg 16   | 6   | 10 | 26 | 100                                                                                 | 1016 M/G |
| Pg 21   | 6,5 | 10 | 32 | 100                                                                                 | 1021 M/G |
| Pg 29   | 8   | 12 | 39 | 50                                                                                  | 1029 M/G |
| Pg 36   | 9   | 15 | 50 | 25                                                                                  | 1036 M/G |
| Pg 42   | 10  | 16 | 57 | 25                                                                                  | 1042 M/G |
| Pg 48   | 10  | 16 | 64 | 10                                                                                  | 1048 M/G |

hexagonal

| A    | L  | SW1 | H  |  | Part No.   |
|------|----|-----|----|-------------------------------------------------------------------------------------|------------|
|      | mm | mm  | mm | Piece                                                                               |            |
| Pg 7 | 5  | 14  | 8  | 100                                                                                 | 10.607 M/G |

| A       | L   | SW1 | H   |  | Part No.   |
|---------|-----|-----|-----|-----------------------------------------------------------------------------------|------------|
|         | mm  | mm  | mm  | Piece                                                                             |            |
| Pg 9    | 6   | 17  | 9   | 100                                                                               | 10.609 M/G |
| Pg 11   | 6   | 20  | 9   | 100                                                                               | 10.611 M/G |
| Pg 13,5 | 6,5 | 22  | 9,5 | 100                                                                               | 10.613 M/G |
| Pg 16   | 6,5 | 24  | 9,5 | 100                                                                               | 10.616 M/G |
| Pg 21   | 7   | 30  | 11  | 100                                                                               | 10.621 M/G |
| Pg 29   | 8   | 40  | 12  | 50                                                                                | 10.629 M/G |
| Pg 36   | 9   | 50  | 15  | 25                                                                                | 10.636 M/G |