

## Smart USB 750VA Tower Line-Interactive 120V UPS with USB port

MODEL NUMBER: **SMART750USB**



### Description

Tripp Lite's SMART750USB line-interactive UPS system offers automatic voltage regulation, surge suppression and long lasting battery support. 750VA/450 watt power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Internal UPS circuits support entry level PC systems for up to 45 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive, black tower configuration. Includes 3 battery-supported outlets for computer, monitor and one vital system peripheral as well as 3 additional surge-only outlets for printers and other system accessories that do not require battery support. USB port (USB cable included) enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert Software available via free download from [www.tripplite.com](http://www.tripplite.com). Built-in dataline protection jacks offer protection of a single dialup phone/DSL line or network Ethernet connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and voltage boost operation. Offers 2.2 minutes battery runtime with a full load of 750VA/450 watts and 8.3 minutes with a half load of 375VA/225 watts. Supports battery replacement via built-in access panel. \$200,000 Ultimate Lifetime Insurance (USA and Canada Only).

### Features

- SMART750USB line-interactive UPS system offers extended voltage regulation (AVR) and battery support as well as complete AC and dialup/DSL/Ethernet line surge suppression
- Supports entry level PC systems for up to 45 minutes during power failures to enable a safe system shutdown
- Supports a max load of 750VA/450 watts for 2.2 minutes and a half load of 375VA/225 watts for 8.3 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 89 volts without using battery power
- Attractive black tower configuration
- Includes 3 battery-supported outlets, plus 3 additional surge-only outlets, 6 foot AC line cord (all NEMA 5-15)
- USB port enables unattended shutdown without data loss during extended power failures; includes USB cable
- Built-in USB port supports on battery, low battery, power restored, AC line voltage, DC battery voltage and battery capacity messaging; interface supports timed inverter shutoff after unattended shutdown, activate self-test and 10 second reboot of connected equipment
- PowerAlert UPS monitoring and unattended shutdown software available via free download from [www.tripplite.com](http://www.tripplite.com)
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked

### Highlights

- 750VA tower 120V line interactive UPS
- Corrects brownouts as low as 89V without using battery power
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- SMART750USB Standby UPS System
- USB and telephone interconnection cables
- Instruction manual with warranty information



- computers by automatically switching UPS power off and back on again (part #WATCHDOGSW)
- Built-in dataline suppression jacks protect a single dialup phone/DSL line or network Ethernet line connection
- Built-in audible alarm and 4 front panel LEDs indicate UPS system and line power status
- 750VA/450 watt power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports battery replacement via built-in access panel
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$200,000 Ultimate Lifetime Insurance (USA and Canada Only)

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	750
Output Watt Capacity (watts)	450
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS input connection description	Angled input plug
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	2.2 min. (450w)
Half load runtime (minutes)	8.3 min. (225w)
DC system voltage (VDC)	12



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Battery recharge rate (included batteries)	Less than 4.5 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	<b>RBC51</b>
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage correction	Input voltages between 89 and 104 are boosted by 14%
<b>LEDS ALARMS &amp; SWITCHES</b>	
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
Alarms	Audible alarm indicates power-failure and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC suppression joule rating	510 joules
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
<b>PHYSICAL</b>	
Installation form factors supported with included accessories	Tower
Installation form factors supported with optional accessories	Wallmount (UPSWM - tower mounting kit)
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10.8 x 5.2 x 7.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	27.3 x 13.3 x 19
UPS / Power Module weight (lbs)	20
UPS / Power Module weight (kg)	9.1
UPS Shipping dimensions (height x width x depth / inches)	14 x 8.5 x 10.5
UPS Shipping dimensions (height x width x depth / cm)	35.6 x 21.6 x 26.7



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping weight (lbs)	22
Shipping weight (kg)	10
UPS housing material	PVC
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	47.3
Battery mode BTU / hr. (full load)	431.5
AC mode efficiency rating (100% load)	97%
<b>COMMUNICATIONS</b>	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	89
High voltage transfer to battery power (setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a href="#">Ultimate Lifetime Insurance</a>

## Related Items

### Optional Products

Model Number	Description	Qty.
<a href="#">DCATV</a>	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
<a href="#">DNET1</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
<a href="#">DTEL2</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
<a href="#">UPSWM</a>	Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)	1
<a href="#">U022-010</a>	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
<a href="#">WATCHDOGSW</a>	WatchDog Service Monitoring / Reboot Software	1
<a href="#">WEXT5-500-1500</a>	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/SMART750USB>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART750USB](#)