

Protective covers - HC-STA-B24-DC-PL - 1421103

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective covers, type: B24, degree of protection: IP20, color: transparent/white

RoHS

Key Commercial Data

Packing unit	5 STK
Minimum order quantity	5 STK
GTIN	 4 055626 251837
GTIN	4055626251837

Technical data

Dimensions

Height	22.1 mm
Width	46.4 mm
Length	123.2 mm

Ambient conditions

Degree of protection of housing (IP)	IP20
Ambient temperature (operation)	0 °C ... 20 °C

General

Size	B24
Color	transparent
Locking type	Clip locking
Material, protective cover	PA
Flammability rating according to UL 94	HB


Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Protective covers - HC-STA-B24-DC-PL - 1421103

Drawings

Dimensional drawing



Approvals

Approvals

Approvals

GL

Ex Approvals

Approval details

GL



<http://exchange.dnv.com/tari/>

6196614 HH

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>