


Dimensions: mm (in.)



Pos. 1	Pos. 2	Pos. 3
(ON)	OFF	(ON)
2-3, 5-6		2-1, 5-4
2 Comm. 5 Comm.	OPEN	2 Comm. 5 Comm.
1 3 4 6		1 3 4 6

SWITCH FUNCTION

Mechanical Specifications:

- Mechanical Life: 30,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Contact Resistance: 10m Ω max. initial @ 2-4 VDC 100mA
- Insulation Resistance: 1,000M Ω min.
- Dielectric Strength: 1,000 V RMS @ sea level
- Rating: 2A/250VAC
5A/120VAC or 28VDC

Note:

- RoHS Compliant by exemption

Soldering Process:

- Manual soldering: Use soldering iron of 30W, controlled at 350°C approx. 5 seconds while applying solder
- Wave soldering: Recommended soldering temperature: 260±5°C Duration of solder immersion: 5±1 seconds
(PCB is 1.6mm in thickness)

Sealed Miniature Toggle Switch

108-1AD4T2226-EVX

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-1AD4T2226-EVX](#)