


Sales Outline DrawingRevision **A****Specifications:**

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	4.0 ~ 7.0
Rated Voltage (Vdc)	6.0
Current Consumption Max. (mA)	30 at Rated Voltage
Sound Pressure Level Min. (dB)	70 at 30cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-40 ~ +70
Storage Temperature (°C)	-40 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: White)
Leading Pins	Tin Plated Brass
Weight (Grams)	9.5
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**

Must connect “-“ to ground; “+” & “C” to positive voltage for operation.