



Wiha Insulated Pliers - Comfort Grip Handle



1000Volt


328 79 25 Pc. Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested.

Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished.

328 79 25 Pc. Master Electrician's Insulated Set

Item# 32879 Set Includes: lbs. 11.0

32808 - 8" Long Nose	32860 - 6.3" Stripping Pliers
32820 - 9" Combination Pliers	61662 - Inch & Metric Folding Ruler
32838 - 8" High Leverage Cutters	15000 - 8.5" Insulated Knife
Slotted: 3.0, 4.5, 6.0mm	Phillips: #1, #2
Square: #1, #2	Terminal Block Driver: #1, #2
Inch Nut Driver: 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"	
Metric Nut Driver: 7.0, 8.0, 10.0, 13.0mm	




1000Volt

328 96 31 Pc. Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested. Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished. Set includes 6ft. Fiber glass folding ruler.

328 96 31 Pc. Master Electrician's Insulated Set

Item# 32896 Set Includes:	lbs. 12.75
32806 - 6.3" Long Nose Pliers	32832 - 6.3" Side Cutters
32808 - 8" Long Nose	32838 - 8" High Leverage Cutters
32816 - 7" Linemans	32860 - 6.3" Stripping Pliers
32820 - 9" Combination Pliers	32870 - 6.3" Round Nose Pliers
Slotted: 2.0, 2.5, 3.0, 3.5, 4.5, 5.5, 6.5, 8.0, 10.0mm	
Phillips: #0, #1, #2, #3	
Inch Nut Driver: 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16"	



1000Volt

328 98 61 Pc. Master Electrician's Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested. Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished. Set includes 6ft. Fiber glass folding ruler.

328 98 61 Pc. Master Electrician's Insulated Set

Item# 32898 Set Includes:	lbs. 24.22
32804 - 8" Bent Nose Pliers	32820 - 9" Combination Pliers
32806 - 6.3" Long Nose Pliers	32832 - 6.3" Side Cutters
32807 - 6.3" Bent Nose Pliers	32838 - 8" High Leverage Cutters
32808 - 8" Long Nose	32846 - 8.3" Cable Cutters
32810 - 6.3" Long Flat Nose	32860 - 6.3" Stripping Pliers
32816 - 7" Linemans	32870 - 6.3" Round Nose Pliers
32255 - Ins Nut Driver 5/32"	32005 - Insulated Slotted 2.0
32258 - Ins Nut Driver 3/16"	32010 - Insulated Slotted 2.5
32261 - Ins Nut Driver 7/32"	32012 - Insulated Slotted 3.0
32264 - Ins Nut Driver 1/4"	32015 - Insulated Slotted 3.5
32267 - Ins Nut Driver 5/16"	32024 - Insulated Slotted 4.5
32270 - Ins Nut Driver 3/8"	32026 - Insulated Slotted 5.5
32273 - Ins Nut Driver 7/16"	32039 - Insulated Slotted 6.5
32276 - Ins Nut Driver 1/2"	32042 - Insulated Slotted 8.0
32278 - Ins Nut Driver 9/16"	32045 - Insulated Slotted 10.0
32280 - Ins Nut Driver 5/8"	32100 - Insulated Phillips #0
32209 - Ins Nut Driver 5.0mm	32101 - Insulated Phillips #1
32212 - Ins Nut Driver 5.5mm	32102 - Insulated Phillips #2
32215 - Ins Nut Driver 6.0mm	32103 - Insulated Phillips #3
32218 - Ins Nut Driver 7.0mm	32521 - Insulated Torx T8
32221 - Ins Nut Driver 8.0mm	32526 - Insulated Torx T9
32227 - Ins Nut Driver 10.0mm	32531 - Insulated Torx T10
32236 - Ins Nut Driver 13.0mm	32536 - Insulated Torx T15
33441 - Ins T-handle Hex 4.0mm	32541 - Insulated Torx T20
33443 - Ins T-handle Hex 5.0mm	32546 - Insulated Torx T25
33445 - Ins T-handle Hex 6.0mm	32551 - Insulated Torx T27
33447 - Ins T-handle Hex 8.0mm	32556 - Insulated Torx T30
33481 - Ins T-handle Hex 5/32"	33485 - Ins T-handle Hex 1/4"
33482 - Ins T-handle Hex 3/16"	33486 - Ins T-handle Hex 5/16"
33483 - Ins T-handle Hex 7/32"	33487 - Ins T-handle Hex 3/8"