




JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
1680	6.0	4.10	32.0	402.2	300	C-6
1295	12.5	3.00	50.0	628.5	300	C-2R
93	12.8	1.04	15.0	188.6	700	C-6
1073	12.8	1.80	32.0	402.2	200	C-6
1156	12.8	2.10	32.0	402.2	1,200	C-6
305	28.0	.51	15.0	188.6	300	*C-2V
1691	28.0	.61	15.0	188.6	1,000	2C-2R
2232	28.0	.643	17.0	213.7	2,000	CC-8
307	28.0	.67	21.0	264.0	300	*C-2V
2233	28.0	.77	21.0	264.0	2,000	CC-8
1665	28.0	.80	21.0	264.0	1,000	*C-2V
1683	28.0	1.02	32.0	402.2	500	2C-6

* SUPPORTED

			METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
			TITLE S-8 SINGLE CONTACT BAYONET BASE LAMP					
DRAWN BY L. WENGSTROM			APP'VD BY DATE J.K. 1/27/03		SIZE A	FSCM NO. 55335	DRAWING NO. BAYONET SINGLE CONTACT S-8	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 5/4/01	REVISION DATE 1/27/03	REV. NO. A	
REV. NO.	DESCRIPTION/ECO NUMBER	APP'VD DATE	SHEET 1 OF 1					