

Voltage and Fiber Optic Snap-On Markers (Non-Adhesive)



Style	Width		Length		Pipe/Conduit O.D. Range		Markers Per Card
	In.	mm	In.	mm	In.	mm	
M	14.00	355.60	23.00	584.20	2.25 – 6.00	57.20 – 152.40	1
R	8.00	230.20	8.00	230.20	.75 – 2.25	19.10 – 57.20	1

Material Chart

Material	Print Method	Temperature Range	Features
Polyester	Pre-Printed	-40°F to 176°F (-40°C to 80°C)	Indoor/outdoor rated; pre-coiled material protects legend from abrasion and chemicals; resistant to UV light chemical atmosphere and abrasion.

Part Number		Legend	Color (Legend/Background)	Std. Pkg. Qty.	Std. Ctn. Qty.
Style M	Style R				
	PCV-120RY	120 Volts	Black/Orange	1	25
	PCV-480RY	480 Volts		1	25
PCV-FOMY	PCV-FORY	Fiber Optic		1	25

Photoluminescent Tapes – Thermal Transfer Printable



Normal Lighting

- Used to mark egress routes, fire alarms, and fire equipment that is clearly visible for up to ten hours after power is lost
- Absorb energy from ambient light and releases this energy in the form of a glow when power is lost
- Can be used in Panduit thermal transfer desktop printers to create direction arrow tape, striped tape, or safety signs on demand
- Panduit photoluminescent tapes meet or exceed the following safety standard specification for photoluminescent safety markings including: ASTM E 2072-00, ASTM E 2073-00, ASTM E 2030-99, DIN67510-1, IMO Resolution A.752.18, ISO/CD 15370, DIN 67510, UL924, ASTM 162, ASTM 648, ASTM 662, MIL-L-3891 B, NFPA 101 Life Safety Code, OSHA 1910.37
- Recommended for use with Photoluminescent Safety Signs see page O.24 for more information

Material Chart

Material	Print Method	Temperature Range	Features
Polyester, Photoluminescent (Y2)	Thermal Transfer (T)	-40°F to 230°F (-40°C to 110°C)	Indoor/outdoor rated; provides durability, high temperature resistance and dimensional stability; does not stretch or easily tear; after power is lost, material emits glow that is clearly visible for up to 10 hours.



Black Light



PT2S-ARW



PT2S-BLK



PT2S-RED

Part Number	Part Description	Width		Roll Length		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	Ft.	m		

Pre-Printed

PT2S-ARW	Photoluminescent, polyester tape, black arrow.	2.00	50.8	30.0	9.1	1	4
PT2S-BLK	Photoluminescent, polyester tape, black stripe.	2.00	50.8	30.0	9.1	1	4
PT2S-RED	Photoluminescent, polyester tape, red stripe.	2.00	50.8	30.0	9.1	1	4

Blank

T200X000Y2T	Photoluminescent, polyester tape.	2.00	50.8	15.0	4.5	1	4
T400X000Y2T	Photoluminescent, polyester tape.	4.00	101.6	15.0	4.5	1	4

Order number of rolls required.

Labels roll mounted on 3.00" cores; when using the TDP43ME thermal transfer desktop printer and 3.00" cores, the roll stand (TDP43M-RS) is required.