

Buss High Voltage Fuses

1000 - 10,000 Volts

HV Series



CATALOG SYMBOL: HVA, HVB, HVJ, HVL, HVR, HVT, HVU, HVW, AND HVX
NON-TIME DELAY
1000 TO 10,000 VOLTS

13/32" and 13/16" x Length
(10.3mm and 20.6mm x Length)
For High Voltage Circuits

- Non-Time Delay fuses for high voltage instruments and circuits.
- Physical size varies with electrical rating of fuse to prevent over-fusing.
- Use HVA, HVB, HVJ and HVL for circuits up to 20kw dc or 30 KVA ac. For higher interrupting capacity, use HVR, HVT, HVU, HVW and HVX.

Test Specifications

Catalog Number	Load	Opening Time
HVA	}	110%
HVB		
HVJ		
HVL		
HVR	}	135%
HVT		
HVU		
HVW		
HVX		

HVA (1000 Volts)

Amps	Dia.	Length		*Wt./100	
		In.	mm	Lbs.	Kg
1/16	3/4				
1/8	1				
1/4	1-1/2				
1/10	2	0.41"	3"	76.1	2
2/10	3				
3/10	4				
3/8	6				
1/2	10				

HVB (2500 Volts)

1/2	1-1/2				
3/4	2	0.41"	4.5"	114.2	3
1	3				

HVJ (5000 Volts)

1/16	1-1/2				
1/8	2				
1/4	4	0.81"	5"	126.9	9
1/2	6				
3/4	10				
1	—				

HVL (10,000 Volts)

1/16	1				
1/8	1-1/2				
1/4	2	0.81"	10"	253.8	15
1/2	3				

HVR (1000 Volts) (max. S.C. KVA-500)

1/2	3				
1	4	0.41"	3"	76.1	3
2	5				

HVT (2500 Volts) (max. S.C. KVA-1250)

1/2	3				
1	5	0.41"	4.5"	114.2	4
2	—				

HVU (5000 Volts) (max. S.C. KVA-2500)

1/2	3				
1	4	0.81"	5"	126.9	19
2	5				

HVW (1200 Volts) (max. S.C. KVA-5000)

1/2	3				
1	4	0.41"	2.25"	57.1	2
2	5				
	8				

HVX (10,000 Volts) (max. S.C. KVA-12,000)

1/2	3				
1	5	0.41"	10.0"	253.8	36

*Shipping.

Carton quantity: 10.

Buss High Voltage Fuses

1000 - 10,000 Volts

HV Series




CATALOG SYMBOL: 4528, 4529, 4530, AND 2960
FUSE BLOCKS

For BUSS High Voltage Fuses (1000 to 10,000 Volts)

- Bakelite base.
- Alloy plated terminals.

Dimensional Data




For Fuse Sym.	Bock Cat. No.	*Dimensions Inches/(mm's)			Base Width
		A	B	C	
HVA	4528	3.75"	1.125"	0.38"	1.0"
HVR		(95.3)	(28.6)	(9.5)	(25.4)
HVB	4529	5.25"	1.125"	0.38"	1.0"
HVT		(133.4)	(28.6)	(9.5)	(25.4)
HVJ	4530	6.5"	1.66"	0.5"	1.38"
HVU		(165.1)	(42.1)	(12.7)	(34.9)
HVL	2960	11.44"	1.45"	0.75"	1.38"
HVX		(290.5)	(48.4)	(19.1)	(34.9)

*Two mounting holes:

Use #8 screws on blocks 4528 and 4529.

Use #10 screws on blocks 4530 and 2960.

Time-Current Characteristic Curves—Average Melt



The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this BIF document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cooper Bussmann:

[HVR-5](#) [HVU-5](#) [HVJ-3/4](#) [HVB-1/2](#) [HVB-2](#) [HVA-2](#) [HVA-1-1/2](#) [HVJ-10](#) [HVJ-4](#) [HVJ-6](#) [HVJ-A-1](#) [HVL-3](#) [HVW-8](#)
[HVU-1/2](#) [HVT-3](#) [HVB-1-1/2](#) [HVA-10](#) [HVA-2-NR](#) [HVA-3](#) [HVA-4](#) [HVA-6](#) [HVB-10](#) [HVB-3](#) [HVB-6](#) [HVE-2](#) [HVE-3/4](#)
[HVA-1/10](#) [HVA-1/16](#) [HVA-1/4](#) [HVA-3/10](#) [HVACSK-45](#)

Eaton:

[HVR-1](#) [HVA-2/10](#) [HVU-2](#) [HVT-2](#) [HVL-1/2](#) [HVL-3/8](#) [HVW-1](#) [HVB-1](#) [HVT-5](#) [HVW-2](#) [HVJ-1/4](#) [HVX-2](#) [HVL-1](#) [HVT-](#)
[1](#) [HVJ-1](#) [HVJ-1-1/2](#) [HVA-3/8](#) [HVL-1-1/2](#) [HVL-1/16](#) [HVL-1/8](#) [HVL-2](#) [HVR-1/2](#) [HVA-1/8](#) [HVR-2](#) [HVX-5](#) [HVW-4](#)
[HVA-1-10](#) [HVA-1-16](#) [HVA-1-4](#) [HVA-3-10](#) [HVE-3-4](#) [HVA-3/4](#) [HVR-4](#) [HVW-5](#) [HVB-3/4](#) [HVT-1/2](#) [HVU-4](#) [HVU-3](#)
[HVA-1/2](#) [HVX-1](#) [HVJ-1/16](#) [HVU-1](#) [HVX-3](#) [HVJ-2](#) [HVX-1/2](#) [HVJ-1/8](#) [HVW-3](#) [HVL-1/4](#) [HVJ-1/2](#) [HVA-1](#) [HVR-3](#)