






## Dimensions: mm (in.)



P.C. Mounting

| POS.1 | POS.2 |
|-------|-------|
|       |       |
| ON    | (ON)  |
| 2-3   | 2-1   |
|       |       |

Switch Function

**Electrical Specifications:**

- Contact resistance: Below 100mΩ typ. initial @ 2-4 V DC, 100mA
- Insulation resistance: 1,000MΩ min.
- Dielectric strength: 500 V RMS min. @sea level
- Rating: 0.4VA max. / 20VAC or DC max.

**Mechanical Specifications:**

- Mechanical life: 40,000 make-and-break cycles
- Operating temperature: -30°C ± 85°C

**Note:**

- RoHS Compliant

**Soldering Process:**

- Wave Soldering: Recommended soldering temperature: 260±5°C  
Duration of solder immersion: 5±1 sec.  
(PCB is 1.6mm in thickness)

**Sealed Ultra-Miniature Toggle Switch**  
108-2US2T1660-EV

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2US2T1660-EV](#)