

Cable duct - CD 100X100 BU - 3240325

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Wiring channel, blue, consisting of upper and lower part, width: 100 mm, height: 100 mm, length: 2000 mm

Why buy this product

- ✓ Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- ✓ Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Key commercial data

Packing unit	0
Minimum order quantity	6
Catalog page	Page 379 (CL2-2011)
GTIN	 4 046356 508056
Custom tariff number	39259020
Country of origin	GERMANY

Technical data

General

Length (b)	2000 mm
Height	100 mm
Width (a)	100 mm
Color	blue
Inflammability class according to UL 94	V0
Ambient temperature (operation)	-5 °C ... 60 °C
Components	Lead-free
Material	PVC

Cable duct - CD 100X100 BU - 3240325

Classifications

eclass

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703

etim

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012

unspsc

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Approvals

Approvals

Approvals

UL Recognized / VDE approval of drawings / CSA

Ex Approvals

Approvals submitted

Approval details

UL Recognized 

VDE approval of drawings 

Cable duct - CD 100X100 BU - 3240325

Approvals



Accessories

Accessories

Cover profile - CD COVER 100 BU - 3240328



Cover for cable duct, blue, width: 100 mm, length: 2000 mm

Fastening clip - RVT-PA 4 - 3240498



Plastic body-bound rivet, 4 mm diameter, for a material thickness of 1.5 ... 6 mm

Fastening clip - RVT-PA 6 - 3240499



Plastic body-bound rivet, 6 mm diameter, for a material thickness of 1.5 ... 6 mm

Tool - UNIFOX-RVT P 4 - 1212478



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

Tool - UNIFOX-RVT P 6 - 1212509



Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

Cable duct - CD 100X100 BU - 3240325

Accessories

Universal wire retaining clip - CD WR - 3240284



Universal wire holding bracket, perforated, for wiring channels

© Phoenix Contact 2012 - all rights reserved
<http://www.phoenixcontact.com>